

SWITCH DISCONNECTOR FUSE 630A, FRAME SIZE 5, 3-POLE FOR LV HRC FUSE SIZE 2 AND 3 FRONT OPERATING LEFT BASIC UNIT WITHOUT HANDLE FLAT TERMINAL WITHOUT FUSES



Model	
Product brand name	SETRON
Product designation	Switching device
Design of the product	3KF switch disconnecter with fuses
Design of the operating mechanism	without
Design of handle	Without
Direction of actuation	from the front
Type of the driving mechanism / motor drive	No
Number of poles	3
Size of disconnecting link	3 and 2
Size of switch disconnecter	5
Size of fuse link	NH2, NH3
Electrical endurance (switching cycles)	
• at AC-23 A / at 440 V / at 50/60 Hz	1 500
• at AC-23 A / at 690 V / at 50/60 Hz	1 000
• at DC-23 A / at 440 V	1 000
I <sup>2</sup> t value	
• with closed switch / for combination switch + fuse / at 500 V / maximum	4 100 000 A <sup>2</sup> ·s

• with closed switch / for combination switch + fuse / at 400 V / maximum	4 100 000 A <sup>2</sup> ·s
• with closed switch / at 690 V / for combination switch + gG fuse / maximum	2 050 000 A <sup>2</sup> ·s
• with closed switch / at 690 V / for combination switch + aM fuse / maximum	2 050 000 A <sup>2</sup> ·s
• of the fuse / at 500 V / maximum permissible	10 400 000 A <sup>2</sup> ·s
• of the gG fuse / at 690 V / maximum permissible	7 000 000 A <sup>2</sup> ·s
• of the aM fuse / at 690 V / maximum permissible	7 000 000 A <sup>2</sup> ·s
<b>Mechanical service life (switching cycles) / typical</b>	6 000
<b>Position / of the switch operating mechanism</b>	at the left end
<b>Fuse system</b>	LV HRC fuse
<b>Overvoltage category</b>	IV
<b>Operating voltage / with current paths in series</b>	
• with degree of pollution 2 / at DC / rated value / Note	440 / 3
• with degree of pollution 3 / at DC / rated value / Note	440 / 3
Insulation voltage / rated value	1 000 V
Surge voltage resistance / rated value	12 kV
<b>Overvoltage in percent / relative to the operating voltage / at AC / at 50/60 Hz</b>	10 %

<b>Protection class</b>	
<b>Protection class IP</b>	IP00
<b>Protection class IP</b>	
• with closed switch / with cover or cable lug cover	IP20
• on the front	IP00

<b>Dissipation</b>	
<b>Power loss [W]</b>	
• with conventional rated thermal current / per pole	40 W
• with conventional rated thermal current / per device	120 W
• with conventional rated thermal current / without fuse / per pole	40 W
• with conventional rated thermal current / without fuse / per device	120 W
• of the fuse / per fuse / maximum	48 W
• maximum	264 W
<b>Operating current</b>	

• at AC-21 A / at 400 V / maximum	630 A
• at AC-21 A / at 500 V / maximum	630 A
• at AC-21 A / at 690 V / maximum	630 A
• at AC-23 A / at 500 V / at 50/60 Hz / rated value / maximum	630 A
• at AC-22 A / at 500 V / at 50/60 Hz / rated value / maximum	630 A
• at AC-22 A / at 400 V / at 50/60 Hz / rated value / maximum	630 A
• at AC-22 A / at 690 V / at 50/60 Hz / rated value / maximum	630 A
• at AC-23 A / at 400 V / at 50/60 Hz / rated value / maximum	630 A
• at AC-23 A / at 690 V / at 50/60 Hz / rated value / maximum	630 A
• at DC-23 A / at 440 V / rated value / maximum	630 A
• at DC-23 A / at 220 V / rated value / maximum	630 A
• at DC-22 A / at 440 V / rated value / maximum	630 A
• at DC-22 A / at 220 V / rated value / maximum	630 A
• at DC-21 A / at 440 V / rated value / maximum	630 A
• at DC-21 A / at 220 V / maximum	630 A
<b>Continuous current</b>	
• rated value	630 A
• at 40 °C / rated value	630 A
• at 45 °C / rated value	630 A
• at 50 °C / rated value	630 A
• at 55 °C / rated value	630 A
• at 60 °C / rated value	630 A
• at 65 °C / rated value	560 A
• at 70 °C / rated value	560 A
Continuous current / at DC / rated value	630 A
<b>Let-through current / of the fuse / at 500 V / maximum permissible</b>	77 400 A
<b>Let-through current / of the gG fuse / at 690 V / maximum permissible</b>	65 000 A
<b>Let-through current / of the aM fuse / at 690 V / maximum permissible</b>	65 000 A
<b>Let-through current / with closed switch</b>	
• at 690 V / for combination switch + aM fuse / maximum permissible	46 590 A
• at 690 V / for combination switch + gG fuse / maximum permissible	46 590 A
• for combination switch + fuse / at 400 V / maximum permissible	58 500 A

<ul style="list-style-type: none"> <li>• for combination switch + fuse / at 500 V / maximum permissible</li> </ul>	58 500 A
Short-time current resistance (I <sub>cw</sub> ) / at 690 V AC/440 V DC / limited to 1 s / rated value	22 kA

### Main circuit

<b>Operating power / at AC-23 A</b>	
<ul style="list-style-type: none"> <li>• at 400 V / at 50/60 Hz / rated value</li> </ul>	355 kW
<ul style="list-style-type: none"> <li>• at 500 V / at 50/60 Hz / rated value</li> </ul>	400 kW
<ul style="list-style-type: none"> <li>• at 690 V / at 50/60 Hz / rated value</li> </ul>	630 kW
<b>Operating voltage</b>	
<ul style="list-style-type: none"> <li>• at AC / at 50/60 Hz / rated value</li> </ul>	690 V
<ul style="list-style-type: none"> <li>• at AC / rated value / maximum</li> </ul>	690 V

### Auxiliary circuit

Number of connected NC contacts / for auxiliary contacts	0
Number of connected NO contacts / for auxiliary contacts	0
Number of connected CO contacts / for auxiliary contacts	0
<b>Suitability for use</b>	
<ul style="list-style-type: none"> <li>• Main switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• switch disconnecter</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• EMERGENCY OFF switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• safety switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• maintenance/repair switch</li> </ul>	Yes
Product feature / interlock	No
<b>Product component</b>	
<ul style="list-style-type: none"> <li>• Voltage trigger</li> </ul>	No
<ul style="list-style-type: none"> <li>• undervoltage release</li> </ul>	No
<ul style="list-style-type: none"> <li>• undervoltage release with leading contact</li> </ul>	No
Product feature / sealable	Yes
<b>Product extension</b>	
<ul style="list-style-type: none"> <li>• Auxiliary switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• optional</li> </ul>	
<ul style="list-style-type: none"> <li>— locking capability</li> </ul>	Yes
<ul style="list-style-type: none"> <li>— motor drive</li> </ul>	No
<ul style="list-style-type: none"> <li>— fuse monitoring</li> </ul>	Yes
<b>Product function</b>	
<ul style="list-style-type: none"> <li>• fuse monitoring</li> </ul>	No

### Short circuit

Short-circuit current making capacity (I <sub>cm</sub> ) / for switch disconnecter / at 690 V AC/440 V DC / without fuse link / rated value / minimum	44 kA
<b>Conditional short-circuit current / with line-side fuse protection</b>	
<ul style="list-style-type: none"> <li>• at 500 V / by gG fuse / rated value</li> <li>• at 690 V / by gG fuse / rated value</li> </ul>	<p>100 kA</p> <p>80 kA</p>

### Connections

Arrangement of electrical connectors / for main current circuit	Top and bottom
<b>Tightening torque / with screw-type terminals</b>	
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	<p>50 N·m</p> <p>75 N·m</p>
<ul style="list-style-type: none"> <li>• Type of connectable conductor cross-sections / for copper busbar</li> <li>• Type of connectable conductor cross-sections / for aluminum conductor / stranded / with lug</li> <li>• Type of connectable conductor cross-sections / for copper conductor / stranded / with lug / acc. to DIN 46234</li> <li>• Type of connectable conductor cross-sections / for copper conductor / stranded / with lug / acc. to DIN 46235</li> </ul>	<p>1x (50x10 mm)</p> <p>1x (25 ... 300 mm<sup>2</sup>), 2x (25 ... 300 mm<sup>2</sup>)</p> <p>1x (25 ... 240 mm<sup>2</sup>), 2x (25 ... 240 mm<sup>2</sup>)</p> <p>1x (25 ... 300 mm<sup>2</sup>), 2x (25 ... 300 mm<sup>2</sup>)</p>
<b>Type of electrical connection</b>	
<ul style="list-style-type: none"> <li>• for main current circuit</li> </ul>	flat connector

### Mechanical Design

<b>Height</b>	270 mm
<b>Width</b>	395 mm
<b>Depth</b>	262 mm
<b>Mounting position</b>	any
<b>Mounting type</b>	floor mounting
<b>Mounting type</b>	
<ul style="list-style-type: none"> <li>• front mounting with 4-hole attachment</li> <li>• front mounting with central attachment</li> <li>• rail mounting</li> </ul>	<p>No</p> <p>No</p> <p>No</p>
<b>Net weight</b>	15 150 g

### Environmental conditions

<b>Degree of pollution</b>	3
<b>Ambient temperature</b>	
<ul style="list-style-type: none"> <li>• during operation / minimum</li> <li>• during operation / maximum</li> <li>• during storage / minimum</li> <li>• during storage / maximum</li> </ul>	<p>-25 °C</p> <p>70 °C</p> <p>-50 °C</p> <p>80 °C</p>

## Certificates

Equipment marking / acc. to DIN EN 61346-2

Q

General Product Approval

other



CCC



VDE

[Miscellaneous](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3KF5363-0LF11>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3KF5363-0LF11>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3KF5363-0LF11](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3KF5363-0LF11)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



