## **Reflex Sensor**

for Roller Conveyor Systems


# **OPT1542**

Part Number



- Energy savings thanks to EcoMode
- Increased capacity thanks to intelligent functions
- Optimized performance
- Time-saving initial start-up with fast-clip mounting system and quick wiring
- Wireless settings via NFC

These sensors have been specially designed for use in accumulation roller conveyors. Their compact design allows for installation between rollers below the transport level. High-precision background suppression makes it possible to reliably detect even black objects at up to 900 mm. Settings are entered via wireless NFC, which is even possible in the de-energized state. Thanks to the innovative fast-clip mounting system and quick wiring, the sensors are installed and ready for use in no time flat.




#### **Technical Data**

Optical Data	
- Range	900 mm
Switching Hysteresis	< 5 %
Light Source	Infrared Light
Wavelength	860 nm
Service Life (T = +25 °C)	100000 h
Risk Group (EN 62471)	1
Max. Ambient Light	90000 Lux
Opening Angle	3 °
Electrical Data	
Supply Voltage	20,630 V DC
Current Consumption Sensor (Ub = 24 V)	< 16 mA
EcoMode	yes
Switching Frequency	100 Hz
Response Time	5 ms
Temperature Drift	< 5 %
Temperature Range	-4060 °C
Number of Switching Outputs	2
Switching Output Voltage Drop	< 0,9 V
PNP Switching Output/Switching Current	200 mA
Short Circuit Protection	yes
Reverse Polarity Protection	yes
Overload Protection	yes
Logic	yes
Single Discharge	yes
Block Forwarding	yes
Solenoid Valve	yes
Automatic Roller Shutdown	yes
Protection Class	III
Mechanical Data	
Setting Method	NFC
Housing Material	Plastic
Degree of Protection	IP65
Connection	M12 × 1; 4-pin
Cable Length	200 cm
Pneumatic Solenoid Valve Unit	
Valve no.	K04
Supply Voltage Valve	19,228,8 V
Current Consumption Valve	86 mA
Valve temperature range	-1550 °C
Operating Pressure	47 bar
Nominal Width	0,8 mm
Nominal flow rate 1 -> 2	20 NL/min
Nominal flow rate 2 -> 3	100 NL/min
Supply-Line Connector Pipe	2× 8×1
Working-Line Connector Pipe	4×1
Valve function	3/2-Way
Switching function	NC
PNP NO/NC switchable	
NFC Receiver Category 3	146
NFC Receiver Category 3 Connection Diagram No.	146 OP3
NFC Receiver Category 3	146 OP3 2 2s

#### **Complementary Products**

o o p. o	
Adapter OPT70N, OPT70S, OPT70P	
Software	
USB NFC Adapter	
ZPTX001 Quick Mount	






### Ctrl. Panel



2a = NFC interface

3a = Switching Status Indicator/Error Indicator



Legen	nd		PT	Platinum measuring resistor	ENAR542	Encoder A/Ā (TTL)
+	Supply Voltage +		nc	not connected	ENBRS42	Encoder B/B (TTL)
-	Supply Voltage 0 V		U	Test Input	ENA	Encoder A
~	Supply Voltage (AC Voltage)		Ū	Test Input inverted	ENB	Encoder B
Α	Switching Output	(NO)	W	Trigger Input	Amin	Digital output MIN
Ā	Switching Output	(NC)	W -	Ground for the Trigger Input	Амах	Digital output MAX
V	Contamination/Error Output	(NO)	0	Analog Output	Аок	Digital output OK
V	Contamination/Error Output	(NC)	0-	Ground for the Analog Output	SY In	Synchronization In
E	Input (analog or digital)		BZ	Block Discharge	SY OUT	Synchronization OUT
Т	Teach Input		Awv	Valve Output	OLT	Brightness output
Z	Time Delay (activation)		а	Valve Control Output +	М	Maintenance
S	Shielding		b	Valve Control Output 0 V	rsv	reserved
RxD	Interface Receive Path		SY	Synchronization	Wire Co	olors according to DIN IEC 757
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black
RDY	Ready		E+	Receiver-Line	BN	Brown
GND	Ground		S+	Emitter-Line	RD	Red
CL	Clock		±	Grounding	OG	Orange
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow
•	IO-Link		Rx+/-	Ethernet Receive Path	GN	Green
PoE	Power over Ethernet		Tx+/-	Ethernet Send Path	BU	Blue
IN	Safety Input		Bus	Interfaces-Bus A(+)/B(-)	VT	Violet
OSSD	Safety Output		La	Emitted Light disengageable	GY	Grey
Signal			Mag	Magnet activation	WH	White
BI_D+/-	Ethernet Gigabit bidirect, data	line (A-D)	RES	Input confirmation	PK	Pink
	Encoder 0-pulse 0-0 (TTL)		EDM	Contactor Monitoring	GNYE	Green/Yellow

## **Switching Distance Deviation**

dSr = Switching Distance Change

Typical characteristic curve based on white, 90 % remission

