

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053072204](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Single Row, 4 Circuits, Natural, Glow-Wire Capable

Documents:

3D Model (PDF)	Product Specification PS-105300-100-001 (PDF)
Drawing (PDF)	Application Specification AS-105300-100-001 (PDF)
3D Model	Packaging Specification PK-105307-100-000 (PDF)
Product Specification 1053001000-PS-CH-000 (PDF)	Test Summary 1053000000-TS-000 (PDF)
Product Specification 1053001000-PS-ES-000 (PDF)	Test Summary 1053001000-TS-000 (PDF)
Product Specification 1053001000-PS-JP-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 1053001000-PS-SK-000 (PDF)	Product Literature (PDF)

Agency Certification

CSA	LR19980
UL	E29179

Application tooling part link

Application Tooling Part Link	63824-4600
-------------------------------	------------

General

Product Family	Crimp Housings
Series	105307
Application	Power, Wire-to-Board
Comments	Operating temperature is -40#C to +105#C for tin and -40#C to +115#C for gold
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
UPC	889056026611

Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.490/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C, -40° to +115°C

Electrical

Current - Maximum per Contact	6.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Application Specification	AS-105300-100-001
Packaging Specification	PK-105307-100-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105307](#) Series

Mates With

Nano-Fit Vertical Headers [1053092104](#) ,
[1053092204](#) , [1053092304](#) , [1053112104](#)
 , [1053112204](#) , [1053112304](#) , [1054312104](#)
 , [1054312204](#) , [1054312304](#) , [1054312404](#)

Nano-Fit Right-Angle Headers
[1053132104](#) , [1053132204](#) , [1053132304](#) ,
[1054302104](#) , [1054302204](#) , [1054302304](#) ,
[1054302404](#)
Nano-Fit Plug Housings
[2002772104](#) , [2002772204](#)

Use With

Nano-Fit Crimp Terminal [105300](#)
Nano-Fit Pre-Crimped Leads (Gold)
[797582129](#) , [797582130](#)
 Nano-Fit Pre-Crimped Leads (Tin)
[797582139](#) , [797582140](#)
 Nano-Fit TPA Retainer [105325](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Product Specification

Sales Drawing

Test Summary

1053001000-PS-CH-000, 1053001000-PS-ES-000,
1053001000-PS-JP-000, 1053001000-PS-SK-000,
PS-105300-100-001
SD-105307-100-000
1053000000-TS-000, 1053001000-TS-000

*Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description

Product #

Description	Product #
Extraction Tool for Nano-Fit Power Connectors and Crimp Terminals, 20-26 AWG	<u>638244600</u>

This document was generated on 10/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION