



| REV | ECO | DESCRIPTION | DATE | BY | APPR |
|-----|-----|-------------------------------|---------|--------|-------|
| A1 | - | NEW DRAWING | 30AUG19 | SULLEN | TOMMY |
| A2 | - | ADD RIBS | 05NOV19 | SULLEN | TOMMY |
| A3 | - | UPDATED SPACE LIMIT DIMENSION | 15JAN20 | SULLEN | TOMMY |
| | | | | | |

REVISIONS





NOTES: UNLESS OTHERWISE SPECIFIED

- 1. MATERIAL: THERMOPLASTIC, BLACK

- SPECIFICATIONS:
 2.1 OPERATING TEMPERATURE: -55°C TO +125°C
 2.2 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C
 - 2.3 MOISTURE RESISTANCE: IP69K (MATED CONDITION) 2.4 MATING CYCLE DURABILITY: 100 CYCLES

 - 2.5 RoHS COMPLIANT
- 3. THIS PRODUCT IS USED WITH AIPXE-325X4A-XXXX AND AIPXE-325X4B-XXXX ENCLOSURE (XXXX= ALL MODIFICATIONS)
- 4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY

| | AIPXE-3 | | 325XBP-01 | | | | · | | |
|--|-------------|--|--------------|-------------|---|------------------|----|--------------|------|
| | PART NUMBER | | | DESCRIPTION | | | | | ITEN |
| QUANTITY | | | MAT | ERI | ALS | S LI | ST | | |
| UNLESS OTHERWISE SPECIFICATIONS: JAI dimension are in metricorium). 2) Tolerances are as follows: IP L DEC a0.16 3) Note reference = MATERIAL SPECIFICATIONS: | | SIGNATURES D | | DATE | Amphanal | | | | |
| | | DRAWN: | SULLEN.ZHANG | 15JAN20 | Ampheno | | | | |
| | | CHECKED: | ORION.LI | 16JAN20 | 44724 Morley Drive Clinton Township, MI 48036 | | | | _ |
| | | ENGINEER: | | | | | | | |
| | | APPROVAL: | TOMMYXIE | 17JAN20 | | | | | |
| | | CUSTOMER: | | | ARMOR IPX | | | | |
| | | THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY, DESIGN FEATURES. | | | BLANK PLATE | | | | |
| PROCESS SPECIFICATIONS: | | SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS. | | B | C- | AIPXE-325XBP-01 | Æ | 13/2 13/2 | |
| NEXT ASS'Y: | | | | SCALE: N | ONE | янеет 1 с | F | 2 | |

ARMOR IPX,BLANK PLATE

