

Product information

13 96 200

Pliers for Electrical Installation

IEC 60900 DIN EN 60900



- 6 functions in one pair of pliers
- Multifunctional pliers for the electrical installation; to grip flat and round material, for bending, deburring, cutting cable, stripping and crimping wire ferrules
- In case of models with opening spring integrated in the joint, the activated locking lever keeps the cutting edges closed while other functions remain active
- The intelligent latching mechanism enables you to "grip" without opening the pliers. The cutting edge remains closed and protected.
- Smooth surfaces near the tips grip single cores without damaging them; serrated gripping surfaces and pipe grip for gripping flat and round material
- Clear-cut outside edge on the gripping surfaces for working on flushmounted junction boxes and deburring feed-through holes
- Stripping holes for conductors of 0.75 1.5 mm² and 2.5 mm²
- Crimping die for wire ferrules 0.5 2.5 mm²
- Cable shears with (induction-hardened) precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm² / Ø 15 mm
- Slim dimensions for easy access
- Bolted joint: precise, zero backlash operation of pliers
- High-grade special tool steel, forged, multi stage oil-hardened

You You Tabe

General	
Article No.	13 96 200
EAN	4003773075110
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	276 g
Dimensions	200 x 85 x 20 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple-	Ø 15 mm

stranded	Ø 15 mm
Cutting capacity copper cable, multiple- stranded	50 mm²
Stripping capacity for cross-sections	0.75 — 1.5 mm² / 2.5 mm²
Capacity in square millimetres	0.5 — 2.5 mm ²
AWG	1/0
VDE tested	yes

technical change and errors excepted



KNIPEX Quality – Made in Germany









