

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2153131043](#)  
**Status:** **Active**  
**Overview:** Mizu-P25 Miniature Waterproof Connectors  
**Description:** Mizu-P25 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Waterproof, Single Row, 600.00mm Length, Tin (Sn) Plating, 4 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">215313</a>
Application	Signal, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Mizu-P25-to-Pigtail
Overview	<a href="#">Mizu-P25 Miniature Waterproof Connectors</a>
Product Name	Mizu-P25 Waterproof
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264682744

**Physical**

Cable Length	600.00mm
Circuits (Loaded)	4
Color - Resin	Black
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Resin	Polyester
Net Weight	17.480/g
Number of Rows	1
Pitch - Mating Interface	2.50mm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-1.90mm
Wire Size AWG	20, 22
Wire/Cable Type	PVC

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2153131041-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
D(2020)4578-DC (25  
June 2020)  
pentacosafuorotridecanoic  
acid  
1,2-  
Benzenedicarboxylic  
acid, dihexyl ester,  
bra  
Terphenyl,  
hydrogenated  
2-(2H-benzotriazol-2-  
yl)-4-(tert-butyl)-6-  
(sec-b  
2-(2H-benzotriazol-2-  
yl)-4,6-  
ditertpentylphenol  
2-ethylhexyl 10-  
ethyl-4,4-dioctyl-7-  
oxo-8-oxa-3,  
sodium  
peroxometaborate  
ammoniumpentadecafluorooctanoate  
disodium 4-  
amino-3-[[4'-[(2,4-  
diaminophenyl)azo]  
1,3-propanesultone  
1-vinylimidazole  
1,2-diethoxyethane  
disodium 3,3'-[[1,1'-  
biphenyl]-4,4'-  
diylbis(azo)  
dodecamethylcyclohexasiloxane  
perfluorooctanoic acid  
di-n-pentyl phthalate  
(DPP)  
furan  
4-o-tolylazo-o-  
toluidine

**China RoHS**

ethylene thiourea  
4-methyl-m-phenylenediamine  
o-toluidine  
butyl 4-hydroxybenzoate  
phenanthrene  
dicyclohexyl phthalate  
p-(1,1-dimethylpropyl)phenol  
N-methylacetamide  
1,2-benzenedicarboxylic acid, dipentylester, bra  
Perfluorohexane-1-sulphonic acid and its salts  
5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5  
1,2-benzenedicarboxylic acid, di-C6-10-alkyl est  
reaction mass of 2-ethylhexyl 10-ethyl-4,4-dioct Cadmium sulphate  
Bisphenol-A  
Methylhexahydrophthalic anhydride  
Perfluorononan-1-oic acid  
(2,2,3,3,4,4,5,5,6,6,7  
Reaction products of 1,3,4-thiadiazolidine-2,5-d  
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o  
Pyrene  
Perfluorobutane sulfonic acid (PFBS) and its sal  
Tris(4-nonylphenyl, branched and linear) phosphi  
Nonadecafluorodecanoic acid (PFDA) and its sodiu  
4-Nonylphenol, branched and linear, ethoxylated  
Trixylyl phosphate  
4-Nonylphenol, branched and linear  
[substances w  
Zirconia  
Aluminosilicate  
Refractory Ceramic Fibr  
Aluminosilicate  
Refractory Ceramic Fibres  
4,4'-Oxydianiline and its salts

Boric acid  
Disodium tetraborate  
n-pentyl-  
isopentylphthalate  
3-ethyl-2-methyl-2-  
(3-methylbutyl)-1,3-  
oxazolidi  
2-benzyl-2-  
dimethylamino-4-  
morpholinobutyropheno  
2-methyl-1-(4-  
methylthiophenyl)-2-  
morpholinoprop  
pentazinc chromate  
octahydroxide  
trilead diarsenate  
arsenic acid  
potassium  
hydroxyoctaoxodizincatedichromate(1-)  
1,2-  
benzenedicarboxylic  
acid; di-C6-8-  
branched a  
1,2,3-trichloropropane  
N-methyl-2-  
pyrrolidone  
1,2-  
benzenedicarboxylic  
acid; di-C7-11-  
branched  
2-ethoxyethyl acetate  
cobalt sulphate  
cobalt dinitrate  
cobalt carbonate  
2-ethoxyethanol  
trichloroethylene  
tetraboron disodium  
heptaoxide, hydrate  
potassium dichromate  
potassium chromate  
Pitch, coal tar, high-  
temp.; Pitch  
Lead chromate  
molybdate sulfate red  
lead chromate  
Anthracene oil,  
anthracene-low;  
Anthracene Oil F  
lead hydrogen  
arsenate  
bis(2-ethylhexyl)  
phthalate (DEHP)  
diarsenic trioxide  
dibutyl phthalate  
(DBP)  
4,4'-  
diaminodiphenylmethane  
bis(2-methoxyethyl)  
phthalate  
dimethyl sulphate  
benzo[a]pyrene  
Fatty acids, C16-18,  
lead salts  
[phthalato(2-)]dioxotrilead

Silicic acid (H<sub>2</sub>Si<sub>2</sub>O<sub>5</sub>),  
barium salt (1:1),  
lead-  
Sulfurous acid, lead  
salt, dibasic  
lead  
bis(tetrafluoroborate)  
dioxobis(stearato)trilead  
tetralead trioxide  
sulphate  
lead titanium trioxide  
lead oxide sulfate  
Silicic acid, lead salt  
lead dinitrate  
cadmium  
lead  
[4-[[4-anilino-1-  
naphthyl]]4-  
(dimethylamino)phen  
1,3,5-  
tris(oxiranylmethyl)-1,3,5-  
triazine-2,4,6(  
Lead oxide  
trilead bis(carbonate)  
dihydroxide  
orange lead  
cadmium oxide (non-  
pyrophoric)  
diboron trioxide  
cadmium carbonate  
N,N,N',N'-  
tetramethyl-4,4'-  
methylenedianiline  
2,2'-dichloro-4,4'-  
methylenedianiline  
dichromium  
tris(chromate)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[215313 Series](#)

**Mates With**

[52213 Mizu-P25 2.50mm Pitch Waterproof Wire-to-Wire Receptacle Housing](#)

This document was generated on 10/15/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**