

HSS centre drill, form A

For universal use up to 1000 N/mm²

ATORN[®]

Application

For centre drilling on conventional and CNC machines.

Version


- spiral-fluted design with relief grinding. diameter 0.5–0.8, ground on one side

Advantage

- Radial relief ensures optimum chip breaking

Delivery

Packing unit: Ref. 005 - 031 = 10 units (price per unit)



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas- tics	Graphite G(C)FK	GG(G) GjMW	Titan- alloy	Nickel- alloy	Super- alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	35	20	10	10		50	70	40	30	35	30	20	10	20					

Art. No.	11001 040
Countersink angle	60 Degree
Cutting material	HSS
Surface	Uncoated
Form	A
Tool holding device	HA parallel shank
Cutting edge diameter	4 mm
Shaft diameter	10 mm
Min./max cutting edge length	5-5.9 mm
Length	56 mm
f steel 700	0.06 mm/r
DIN	333

EAN-Code

4050293011753