

grinding and control vices, type PL-S MICRO

Operated with hexagon socket key




Application:

For horizontal, vertical and lateral grinding, inspection and eroding tasks.

Execution:

- Made of alloyed tool steel.
- Hardened and precision-ground.
- Quick adjustment.
- Perpendicularity tolerance 0.005 mm/100 mm (base area to fixed jaw clamping surfaces).
- Ref. no. 110-150, parallelism tolerance 0.002 mm/100 mm (base area to upper guide plate).
- Ref. no. 110-120: type PL-S MICRO, ref. no. 130-150: type PL-S.



Art. no.	28600 140
Brand	RÖHM
Manufacturer Part Number	1179517
Model	Type PL-S with quick adjustment
Prism countersunk horizontally and vertically	Yes
Jaws width	90 mm
Jaws height	40 mm
Height 2	40 mm
Clamping width	120 mm
Height	80 mm
Body length	210 mm
Length 2	40 mm
Length 3	50 mm
Gross Weight	6.295 kg
Product Group	202

EAN

4019208228259