

## Test pump UX 60, 0 to 60 bar

With 10-L rectangular container



### Application:

For hydrostatic testing of parts such as fittings, pipes, pipelines, tanks, gas bottles, test stands and many other high-pressure components.

### Execution:

- Test media: clear water, water/oil emulsion, hydraulic oil or low viscosity oil
- With drain valve, manometer and stainless steel container
- With 2-m pressure hose DN 10

<b>Art. no.</b>	<b>56377 003</b>
<b>Brand</b>	URACA
<b>Manufacturer Part Number</b>	W2828-E
<b>Model</b>	UX 60
<b>Bin capacity</b>	10 l
<b>Min./max. pressure</b>	0-60 bar
<b>Design</b>	Stationary
<b>Connection thread</b>	G 1/2 inch
<b>Form</b>	Rectangular
<b>Feed volume per stroke</b>	11 cm <sup>3</sup>
<b>Length x width x height</b>	500 x 180 x 160 mm
<b>Material</b>	Stainless steel
<b>Weight</b>	6.5 kg
<b>Gross Weight</b>	7.920 kg
<b>Product Group</b>	575

