

Solid carbide end mill

4 cutting edges, TiAlN-coated


ORION[®]

Application:

End mill for universal machining of non-ferrous metals.

Execution:

- solid carbide ultra-fine grain
- straight shank in accordance with DIN 6535 HB
- TiAlN-coated
- centre cutting
- with edge protection chamfer



Art. no.	16828 200
Brand	ORION
Manufacturer Part Number	16828200
Cutting material	SC
Surface	TiAlN
Type	W
Number of cutting edges	4 PCS
Twist angle	45°
Tool holding device	HB parallel shank
Construction length	Normal
Cutting edge diameter	20 mm
Cutting edge length	38 mm
Length	104 mm
Edge protection chamfer length	0.2 mm
Shank diameter	20 mm
fz aluminium	0.1 mm
Gross Weight	0.405 kg
Overall stainless steel suitability	2
fitness not iron total	1
fitness Titan/Nickel/Super total	2
Product Group	154

EAN

4039247455614