

Micromar 40 EWR-V electronic micrometer set

with sliding spindle and interchangeable slides



Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- Reset
- LOCK function
- mm/inch changeover
- AUTO OFF
- Origin (measurement presetting)
- ABS function
- HOLD (measured value storage)
- TOL (input of tolerances and warning limits)
- EWR-V: MultiCom data output

Advantage:

- Digit height 10 mm
- Non-rotating spindle
- QUICK DRIVE quick adjustment
- Includes 6 pairs of exchangeable gauge slides

Delivery:

incl. operating instructions, battery, case and 1 each of the following gauge slide pairs: 40 Ef planar dia. 6.5 mm, 40 Ea stepped dia. 2 x 4 mm, 40 Et plate dia. 11.3 mm, 40 Eb spherical R=5 mm, 40 Ep tapered 60° 0.3-5.5 mm, 40 Es blade-type 0.75 x 4 mm



Art. no.	31403 574
Brand	MAHR
Manufacturer Part Number	4157050
Min./max. length measuring range	0-25 mm
Digit increment	0.001 mm
Data transmission type	multiCOM
Measuring surface diameter	6.5 mm
IP protection class	IP 65
Functions	ABS function
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
Calibration Group	D
Gross Weight	1.800 kg
Product Group	305

EAN

4059192058609