

CM-PVS.41P



CM-PVS.41P Three-phase monitoring relay 2c/o, 0,0.1-30s, L1-L2-L3=3x300-500VAC

General Information

Extended Product Type	CM-PVS.41P
Product ID	1SVR740794R3300
EAN	4016779852029
Catalog Description	CM-PVS.41P Three-phase monitoring relay 2c/o, 0,0.1-30s, L1-L2-L3=3x300-500VAC
Long Description	The CM-PVS.41P relay is from the CM three-phase monitors range. This relay operates with a rated control supply voltage / three-phase measuring voltage of 300-500 V AC and has a 2 c/o output with contacts rated at 250 V / 4 A. The CM-PVS.41P monitors the phase parameters over/undervoltage and phase failure. The corresponding threshold values are adjustable. Phase sequence monitoring as well as an ON or OFF tripping delay are selectable. The tripping delay is adjustable over a range of instantaneous to 30 s (0, 0.1-30 s). A sealable transparent cover for protection against unauthorized changes is available as accessory. The device offers maintenance free Easy Connect Technology with push-in terminals.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Popular Downloads

Data Sheet, Technical Information	2CDC112211D0201
Instructions and Manuals	1SVC730510M0000

Dimensions

Product Net Width	22.5 mm
Product Net Depth / Length	103.7 mm
Product Net Height	85.6 mm
Product Net Weight	0.131 kg

Technical

Function	Phase failure detection Phase sequence monitoring Over- and undervoltage monitoring
Standards	CAN/CSA C22.2 No.14 EN 50581 IEC/EN 60255-27 IEC/EN 61000-6-2 IEC/EN 61000-6-3 UL 508

Measuring Range	(L-L) 300 ... 500 V AC
Rated Control Supply Voltage (U_s)	(L-L) 300 ... 500 V AC
Rated Frequency (f)	Supply Circuit 50/60 Hz
Output	2 c/o (SPDT) contacts
Time Range	200 ms start-up delay 0 s or 0.1 ... 30 s tripping delay (ON or OFF)
Terminal Type	Screwless Terminals
Rated Operational Current AC-12 (I_{θ})	(230 V) 4 A
Rated Operational Current AC-15 (I_{θ})	(230 V) 3 A
Rated Operational Current DC-12 (I_{θ})	(24 V) 4 A
Rated Operational Current DC-13 (I_{θ})	(24 V) 2 A
Minimum Switching Capacity	24 V 10 mA
Rated Insulation Voltage (U_i)	Input Circuit / Output Circuit 600 V Output Circuit 1 / Output Circuit 2 300 V
Rated Impulse Withstand Voltage (U_{imp})	Input Circuit 6 kV Output Circuit 4 kV
Degree of Protection	Housing IP50 Terminals IP20
Overvoltage Category	III
Pollution Degree	3
Short-Circuit Protective Devices	Output Circuit NC - F Type Fuses 6 A Output Circuit NO - F Type Fuses 10 A
Electrical Durability	AC-12 100000 cycle
Mechanical Durability	30000000 cycle
Connecting Capacity	Flexible with Ferrule 2x 0.5 ... 1.5 mm ² Flexible with Insulated Ferrule 2x 0.5 ... 1.5 mm ² Flexible 2x 0.5 ... 1.5 mm ² Rigid 2x 0.5 ... 1.5 mm ²
Wire Stripping Length	8 mm
Mounting Position	Any
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715

Environmental

Ambient Air Temperature	Operation -25 ... +60 °C Storage -40 ... +85 °C
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Output Circuit 300 V AC
Contact Rating UL/CSA	B300
Connecting Capacity UL/CSA	Flexible 2x 18-16 AWG Rigid 2x 20-16 AWG

Certificates and Declarations (Document Number)

CCC Certificate	CCC_2009010303326655
cULus Certificate	cULus508_20120829-E140448
Declaration of Conformity - CE	1SVD981014-0002

DNV GL Certificate	DNV_GL_TAA000017D
EAC Certificate	EAC_RU_C-DE.ME77.B.03424
Environmental Information	1SAA981020-2401
Instructions and Manuals	1SVC730510M0000
RMRS Certificate	RMRS_1740020250
RoHS Information	1SVD981014-0002

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	97 mm
Package Level 1 Height	109 mm
Package Level 1 Depth / Length	30 mm
Package Level 1 Gross Weight	0.156 kg
Package Level 1 EAN	4016779852029

Classifications

Object Classification Code	B
ETIM 4	EC001441 - Phase monitoring relay
ETIM 5	EC001441 - Phase monitoring relay
ETIM 6	EC001441 - Phase monitoring relay
ETIM 7	EC001441 - Phase monitoring relay
eClass	7.0 27371803
UNSPSC	39121536
E-Number (Sweden)	3860603

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Three Phase Monitors

