

- Low profile socket, sits only .122" above PCB.
- Hi-Rel, 4-finger BeCu #30 clip rated at 3 amps. See page 208 for details.
- Uses Mill-Max #0501 pin. See page 131 for details.

Total number of pins				Quantity per tube	<h3>Ordering Information</h3>
	A	B	C		

10	0.5	0.2	0.3	41	115-XX-210-41-001000
4	0.2	0.3	0.4	102	115-XX-304-41-001000
6	0.3	0.3	0.4	67	115-XX-306-41-001000
8	0.4	0.3	0.4	50	115-XX-308-41-001000
10	0.5	0.3	0.4	40	115-XX-310-41-001000
14	0.7	0.3	0.4	28	115-XX-314-41-001000
16	0.8	0.3	0.4	25	115-XX-316-41-001000
18	0.9	0.3	0.4	22	115-XX-318-41-001000
20	1.0	0.3	0.4	20	115-XX-320-41-001000
22	1.1	0.3	0.4	18	115-XX-322-41-001000
24	1.2	0.3	0.4	16	115-XX-324-41-001000
28	1.4	0.3	0.4	14	115-XX-328-41-001000
20	1.0	0.4	0.5	20	115-XX-420-41-001000
22	1.1	0.4	0.5	18	115-XX-422-41-001000
24	1.2	0.4	0.5	16	115-XX-424-41-001000
28	1.4	0.4	0.5	14	115-XX-428-41-001000
32	1.6	0.4	0.5	12	115-XX-432-41-001000
24	1.2	0.6	0.7	16	115-XX-624-41-001000
28	1.4	0.6	0.7	14	115-XX-628-41-001000
32	1.6	0.6	0.7	12	115-XX-632-41-001000
36	1.8	0.6	0.7	11	115-XX-636-41-001000
40	2.0	0.6	0.7	10	115-XX-640-41-001000
42	2.1	0.6	0.7	9	115-XX-642-41-001000
48	2.4	0.6	0.7	8	115-XX-648-41-001000
50	2.5	0.6	0.7	8	115-XX-650-41-001000
52	2.6	0.6	0.7	7	115-XX-652-41-001000
50	2.5	0.9	1.0	8	115-XX-950-41-001000
52	2.6	0.9	1.0	7	115-XX-952-41-001000
64	3.2	0.9	1.0	6	115-XX-964-41-001000

**XX= Plating Code
See Below**

For RoHS compliance, select ◇ plating code. For the all gold option (XX=13) also change part number from 115-XX-XXX-41-001000 to 115-13-XXX-41-001100

**RoHS
2002/95/EC**

SPECIFY PLATING CODE XX=	13 ◇		93		43 ◇
Sleeve (Pin)	10μ" Au		200μ" Sn/Pb		200μ" Sn
Contact (Clip)	30μ" Au		30μ" Au		30μ" Au