

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1552200064](#)  
**Status:** **Active**  
**Overview:** [Flamar Standard Cables for Industrial Automation](#)  
**Description:** Flamar Sensor Cable, WSOR Jacket, Unshielded, 4 Circuits, 22 AWG, 5.10mm Diameter, 600.0m Length, Black

**Documents:**

[Product Specification 1552200001-P1E \(PDF\)](#)      [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">155220</a>
Bending Radius - Minimum	> 7.5xOD
Color - Cable Jacket	Black
Comments	3 reels of 200.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Material - Outer Jacket	WSOR
Outer Jacket Diameter	5.10mm (.201")
Overview	<a href="#">Flamar Standard Cables for Industrial Automation</a>
Product Literature Order No	987651-3992
Product Name	Flamar
UPC	889056457880

**Physical**

Cable Length	600.0m
Circuits (Loaded)	4
Insulation	TPE
Net Weight	0.010/g
Packaging Type	Reel
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	22
Wire Size mm <sup>2</sup>	0.34
Wire/Cable Type	Signal and Control, UL AWM 21215 / CSA

**Electrical**


Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

**Material Info**

Engineering Number	B30-4-3X200M
--------------------	--------------

**Reference - Drawing Numbers**

Product Specification	1552200001-P1E
-----------------------	----------------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[155220](#) Series

**Use With**

Nano-Change® (M8) [120091](#) , Micro-Change® (M12) [120071](#) , Ultra-Lock® (M12) [120085](#)