

Scissor-type lifting table carriages

Carrying capacity: up to 1500 kg

Application:

Lift, lower and transport using just one device, for use as an adjustable serving trolley at assembly workplaces and as the ideal workshop and supply trolley with a wide range of commercial and industrial uses.

Execution:

- For loads from 150 kg up to 1500 kg, lifting heights from 225 mm to 1510 mm
- Stable scissor-type bracing
- Hand handle control, continuous height adjustment
- Lift operation via pedal
- Hydraulic pump made of high-strength steel
- 2 steering wheels with wheel block, 2 axis wheels
- Polyurethane wheels (PU) for low-noise and easy run
- Pressure relief valve for long life of the pump
- Colour: RAL 5012, light blue, powder-coated



Art. no.	50262 905
Load-carrying capacity	300 kg
Min. table height	340 mm
Max. table height	900 mm
Stroke height per pedal movement	15 mm
Loading surface length	855 mm
Loading-surface width	500 mm
Loading surface thickness	50 mm
Shear design	Single
Colour	Light blue RAL 5012
Surface	Powder-coated
Number of steering rollers	2 PCS
Number of fixed rollers	2 PCS
Stroke mechanism	Manual
Lift height	560 mm
Length	1165 mm
Width	500 mm
Height	970 mm
Gross Weight	83.000 kg
Product Group	559

EAN

4260151123140