


Data sheet for three-phase Squirrel-Cage-Motors



MLFB-Ordering data : 1LA7113-4AA66

without (standard)

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data:

Rated voltage :	(6) 400 VD/690 VY, 50 Hz, 460 VD, 60 Hz					
Frequency :	50 Hz		60 Hz			
Rated power :	4.00 kW		4.60 kW			
Rated speed :	1440 1/ min		1740 1/ min			
Rated torque :	26.5 Nm		25.2 Nm			
Rated current (IE) :	VD	VY	VD			
	8.40 A	4.87 A	8.00 A			
Starting / rated current :	6.0		7.2			
Breakdown / rated torque :	3.0		3.0			
Starting / rated torque :	2.7		2.7			
	4/4	3/4	2/4	4/4	3/4	2/4
Efficiency %	83.1%	83.1%	82.1%	85.0%	85.0%	84.0%
Power factor :	0.83	0.79	0.89	0.84	0.80	0.71
Efficiency class :	IE1		IE1			

Mechanical data:

Sound pressure level 50Hz/60Hz (load) :	53 dB(A)	57 dB(A)
Moment of inertia :	0.012 kg*m ²	
Bearing DE :	6206 2ZC3	
Bearing NDE :	6205 2ZC3	
Type of bearing :	Floating bearings pre-loaded DE (standard)	
Condensate drainage holes :	No	
Regreasing device :	No	
Lubricants :	Esso Unirex N3	
Grease lifetime/Relubrication interval :	40000 h	
Quantity of grease for relubrication :	null g	
External earthing terminal :	No	
Coating :	Special paint finish RAL 7030 stone gray	

Environmental conditions:

Ambient temperature :	-20 °C - +40 °C
Altitude above sea level :	1000 m
Standards and specifications :	IEC, DIN, ISO, VDE, EN

General data:

Frame size	112 M
Design of rotating electrical machines :	(6) IM B35
Weight in kg, without optional accessories :	31.00 kg
Frame material :	Aluminum
Degree of protection :	IP 55
Method of cooling, TEFC :	IC 411
Vibration class :	A (Standard)
Insulation :	155(F) to 130(B)
Duty type :	S1 - continuous duty
Direction of rotation :	Bi-directional

Terminal box:

Material of terminal box :	Aluminum
Type of terminal box :	gk 130
Contact screw thread :	M4
Max. cross-sectional area :	4.00 mm ²
Cable diameter from ... to ... :	11.00 mm - 21.00 mm
Cable entry :	2xM32x1,5
Cable gland :	2 plugs

Special design: