

Appliance trolley with support wheels, pneumatic tyres

Load-bearing capacity 400 kg

fetra
Transportgeräte

Application:

For transporting large loads such as boilers on flat surfaces and especially on stairs

Execution:

- Very sturdy welded steel tube structure
- Supports with wide rubber profiles
- Toe plate with non-slip coating
- Support wheels, solid rubber, 160 x 40 mm, „no tracks“. As a result, the cart can be moved effortlessly when in a lowered state
- Locking device on the support wheels. This means that the support wheels can be used as brakes when descending stairs
- Height-adjustable handle bar can be rotated by 180°. This means that the grip position can be adjusted optimally for any transport situation

Delivery:

With pneumatic wheels. Without wheel spiders, without carrier spars, without tensioning belt.



Art. no.	50270 392
Brand	FETRA
Manufacturer Part Number	11051
Toe plate width	550 mm
Height	1300 mm
Toe plate depth	190 mm
Material of wheel	Air
Load-carrying capacity	400 kg
Width	700 mm
Surface	Powder-coated
Wheel diameter	300 mm
Material	Steel pipe
Total stop optional	No
Gross Weight	39.000 kg
Product Group	5AB

EAN

4017976110509