

Blind rivet nut hand tool

GBM 50



Version:

- Quick drill setup – fast and easy to drill into and drill out blind rivet nuts
- Ergonomic design, low effort, optimised leverage
- Sets blind rivet nuts up to M12
- Threaded mandrels and mouthpieces can be changed quickly and without tools

Delivery:

Set in a plastic carrying case with mouthpieces/threaded mandrels M5, M6, M8, M10, installation key and operating instructions

Art. no.	53195 303
Model	GBM 50
Length	485 mm
Suitable for max. rivet diameter (rivet material: aluminium)	12 mm
Suitable for max. rivet diameter (rivet material: stainless steel)	10 mm

EAN-Code

4007081092487

