

KFM 18 LTX 3 RF cordless metal router

18 volts, no battery pack or charger

metabo®

Application:

The most powerful cordless metal router for 45° chamfers up to 4 mm and radii of 2 and 3 mm

Execution:

- Oxide-free and burr-free surfaces in ideal preparation for applying powder or paint coatings for maximum corrosion protection
- One-touch controller: patented tool-free milling depth adjustment in 0.1 mm increments; detent points for short adjustment times, which prevent accidental adjustment of cutting depth when working
- Slim milling head for working in pipes and holes from dia. 13 mm and on outer contours
- Parallel stop for a uniform result when processing straight edges
- Ergonomic thanks to its lightweight and compact design.
- High removal rate with low physical effort and continuous speed adjustment for different materials.
- Comprehensive user protection through soft start function, restart protection, blockage monitoring and electronic overload protection.



Advantage:

- Rotatable battery pack for better working in confined spaces
- Removable dust protection filter protects motor from coarse particles

Delivery:

Does not include battery or charger, 2 cemented carbide indexable inserts, 45° chamfer, 2 cemented carbide indexable inserts radius R2, 2 cemented carbide indexable inserts R3, guide stop, TX 15 screwdriver, bow handle, dust protection filter, MetaLoc case

Art. no.	70377 501
Battery included	No
Number of rechargeable batteries/batteries	0
Battery voltage	18 V/AC
Max. idle speed	7000 rpm
Max. chamfer height 45°	4 mm
Max. chamfer width 45°	6 mm
Max. radius	3 mm
With soft start	Yes
With restart protection	Yes
With overload protection	Yes
Weight	3.1 kg
Product Group	Prod. Gr. 745

EAN

4007430291462