




Produktinformation Managed Gigabit Ethernet RSP Switches - RSP35-0803306TTSCCV9HPE2S04.0.

Industrial Ethernet:Power Rail Switches:RSP Switches:with HiOS 4.0:Managed Gigabit Ethernet RSP Switches

<https://e-catalog.beldensolutions.com:443/link/57078-24455-202442-279205-412488-412490/de/RSP35-0803306TTSCCV9HPE2S04.0./uistate>

Name	Managed Gigabit Ethernet RSP Switches
	
	Managed, Industrial Switch DIN Rail, lüfterloses Design. Fast Ethernet, Gigabit Uplink type. Enhanced Redundancy (PRP, Fast MRP, HSR).
Lieferinformationen	
Lieferstatus	bestellbar
Produktbeschreibung	
Beschreibung	Managed, Industrial Switch DIN Rail, lüfterloses Design. Fast Ethernet, Gigabit Uplink type. Enhanced Redundancy (PRP, Fast MRP, HSR).
Port-Typ und Anzahl	11 Ports insgesamt, davon Fast Ethernet Ports: 8 x 10/100BASE TX / RJ45; davon Uplink Ports: 3 x Gigabit Ethernet SFP slots (1000 MBit).
Typ	RSP35-0803306TTSCCV9HPE2S04.0.
Bestell-Nr.	RSP35-0803306TTSCCV9HPE2S04.0.
Weitere Schnittstellen	
Versorgung/Meldekontakt	2 x steckbarer Klemmblock 2-polig, 1 x steckbarer Klemmblock 2-polig
V.24 Zugang	1 x RJ11 Buchse
SD-card slot	1 x SD Card Slot zum Anschluss des Autokonfigurationsadapters ACA31
Netzausdehnung-Leitungslängen	
Twisted Pair (TP)	0 m ... 100 m
Multimode-Faser (MM) 50/125 µm	siehe SFP LWL-Modul M-SFP-SX/LC und M-SFP-LX/LC
Multimode-Faser (MM) 62,5/125 µm	siehe SFP LWL-Modul M-SFP-SX/LC und M-SFP-LX/LC
Singlemode-Faser (SM) 9/125 µm	siehe SFP LWL-Modul M-SFP-LX/LC
Singlemode-Faser (LH) 9/125µm (Long Haul-Transceiver)	siehe SFP LWL-Modul M-SFP-LH/LC und M-SFP-LH+/LC
Netzausdehnung-Kaskadertiefe	
Linien-/Sternstruktur	beliebig
Versorgung	
Betriebsspannung	2 x 24/36/48 VDC (18-60 VDC)
Software	
Management	LLDP (802.1AB), SSHv2, V.24, HTTP, HTTPS, Traps, SNMP v1/v2/v3, Telnet
Diagnose	Management address conflict detection, TFTP, SFTP, SCP, LLDP-MED, MAC notification, Signal contact, Device status indication, TCPDump, LED, Syslog, Persistent logging on ACA21/31, Port Monitor, Duplex mismatch detection, RMON (1,2,3,9), Port mirroring 1:1, Port mirroring N:1, System information, Self tests on cold start, Copper cable test, SFP management (temperature, optical input and output power), Configuration check dialog, Switch dump, Snapshot configuration feature
Konfiguration	Automatic configuration undo (roll-back), Text based configuration file (XML), BOOTP/DHCP client with auto configuration, DHCP Server: Per port, DHCP Server: Pools per VLAN, Auto-configuration adapter ACA31 (SD card), HiDiscovery, DHCP relay with option 82, Command line interface (CLI), CLI scripting, Full featured MIB support, WEB based management
Sicherheit	MAC based port security, Port-based access control with 802.1X, Guest/unauthenticated VLAN, Integrated Authentication Server (IAS), RADIUS VLAN assignment, Automatic Denial-of-Service Prevention, VLAN based ACL, Ingress VLAN based ACL, Basic ACL, Device security indication, Audit trail, CLI logging, HTTPS certificate management, Restricted management access, Configurable password policy, Configurable number of login attempts, SNMP logging, Different privilege levels, Local user management, Remote authentication via RADIUS, Account locking
Redundanzfunktionen	Link Aggregation, Link Backup, MRP (Media Redundancy Protocol IEC62439-2), IEC62439-3 redundancy Fast MRP, HSR (High Availability Seamless Redundancy Protocol), PRP (Parallel Redundancy Protocol), RSTP 802.1D-2004 (IEC62439-1)
Filter	Independent VLAN learning, Fast aging, Static unicast/multicast address entries, QoS / Port priority (802.1D/p), TOS/DSCP prioritization, Interface trust mode, CoS queue management, VLAN (802.1Q), Voice VLAN, IGMP snooping/querier per VLAN (v1/v2/v3), Unknown multicast filtering, MVRP (Multiple VLAN Registration Protocol), MMRP (Multiple MAC Registration Protocol), MRP (Multiple Registration Protocol)
Industrial Profiles	IEC61850 protocol (MMS Server, Switch Model)
Zeitsynchronisation	SNTP Server and Client, PTPv2 TC two-step, PTPv2 BC, Buffered RTC
Flow Control	Flow control (IEEE802.3X), egress interface shaping, ingress storm protection, Queue-Shaping / max. Queue Bandwidth



Industrial Ethernet: Power Rail Switches: RSP Switches: with HiOS 4.0: Managed Gigabit Ethernet RSP Switches

<https://e-catalog.beldensolutions.com:443/link/57078-24455-202442-279205-412488-412490/de/RSP35-0803306TTSCCV9HPE2S04.0./uistate>

Sonstiges	Portabschaltung, automatische Kabelanpassung, zweifaches Betriebssystem, VLAN unaware mode, durch VLAN beschränkter Managementzugang.
Zulässige Umgebungsbedingungen	
Betriebstemperatur	0 °C ... 60 °C
Lager-/Transporttemperatur	-40 °C ... 70 °C
Rel. Luftfeuchte (nicht kondensierend)	10 % ... 95 %
Konstruktiver Aufbau	
Abmessungen (B x H x T)	90 mm x 164 mm x 120 mm
Montage	Hutschiene
Gewicht	1200 g
Schutzart	IP30
Mechanische Stabilität	
IEC 60068-2-27 Schock	15 g, 11 ms Dauer, 18 Schocks
IEC 60068-2-6 Vibration	1 mm, 2 Hz-13,2 Hz, 90 min.; 0,7 g, 13,2 Hz-100 Hz, 90 min.; 3,5 mm, 3 Hz-9 Hz, 10 Zyklen, 1 Oktave/min.; 1 g, 9 Hz-150 Hz, 10 Zyklen, 1 Oktave/min
EMV-Störfestigkeit	
EN 61000-4-2 Elektrostatische Entladung (ESD)	8 kV Kontaktentladung, 15 kV Luftentladung
EN 61000-4-3 Elektromagnetisches Feld	35 V/m (80-2700 MHz); 1 kHz, 80% AM
EN 61000-4-4 Schnelle Transienten (Burst)	4 kV power line, 4 kV data line
EN 61000-4-5 Stoßspannungen (Surge)	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line, IEEE1613: power line 5 kV (line/earth)
EN 61000-4-6 Leitungsgeführte Störspannungen	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)
EN 61000-4-16 Niederfrequente Störungen	30 V, 50 Hz gleichbleibend; 300 V, 50 Hz 1 s
EMV-Störaussendung	
FCC CFR47 Part 15	FCC 47 CFR Part 15 Class A
EN 55022	EN 55022 Class A
Zulassungen	
Bahnnorm	EN50121-4
Substation	IEC 61850-3, IEEE 1613
Transportation	NEMA TS2 (in Vorbereitung)
Lieferumfang bzw. Zubehör	
Lieferumfang	Gerät, Klemmenblock, Bedienungsanleitung

Für weitere Informationen kontaktieren Sie bitte:

Hirschmann Automation and Control GmbH

Stuttgarter Straße 45-51

72654 Neckartenzlingen

Germany

Tel +49 7127/14-1809

E-Mail: inet-sales@belden.com

Die auf den Webseiten veröffentlichten Informationen sind mit größtmöglicher Sorgfalt zusammengestellt. Sie unterliegen dem Vorbehalt der jederzeitigen Änderung, sowohl in technischer als auch in preislich/kommerzieller Hinsicht. Die vollständigen Informationen und Daten entnehmen sie bitte der Anwenderdokumentation. Verbindliche Aussagen können nur auf konkrete Anfragen hin abgegeben werden.