

## DULUX D/E 26 W/827

OSRAM DULUX D/E | CFLni, 2 tubes, with 4-pin base for ECG operation



#### Areas of application

- Offices, public buildings
- Shops
- Supermarkets and department stores
- Hotels, restaurants
- Industry

#### Product benefits

- Extremly economical
- Good quality of light
- Excellent luminous flux
- Long service life
- Improved maintenance
- OSRAM System+ Guarantee in combination with OSRAM QUICKTRONIC ECG

#### Product features

- Average life: 20,000 h (with QUICKTRONIC)
- Color rendering index R<sub>2</sub>: 80...89
- Dimmable (3...100 %)
- Short and compact pin-base lamp with double-turn tubes
- Single-ended four-pin plug-in G24q base
- Operates on battery, solar and AC power with suitable electronic control gear



### Technical data


### **Electrical data**


Nominal wattage	26.0 W			
Rated wattage	26.00 W			
Rated lamp efficacy (HF data 25 °C)	Under clarification by authority and standardization body			


### Photometrical data

Nominal luminous flux	1710 lm		
Rated luminous flux	1710 lm		
Color temperature	2700 К		
Light color	827		
Light color as per EN 12464-1	LUMILUX INTERNA		
Color rendering index Ra	8089		
Luminous flux at 25 °C 1800 lm			
Rated LLMF at 4,000 h	0.84		
Rated LLMF at 6,000 h	0.82		
Rated LLMF at 8,000 h	0.81		
Rated LLMF at 12,000 h	0.79		
Rated LLMF at 16,000 h	0.78		
Rated LLMF at 20,000 h	0.76		
Luminance	5.5 cd/cm <sup>2</sup>		
Color rendering group	18		

### **Dimensions & weight**







Overall length	169.5 mm
Product weight	48.80 g
Tube diameter	12 mm

Length	169.5 mm
Length acc. to IEC standard	160 mm
Length with base excl. base pins/connection	149.00 mm

### Temperatures

Rated ambient temp.w.max.luminous flux	25.0 °C

### Lifespan

Nominal lamp life time	10000 h			
Rated lamp life time	10000 h			
Service life	13000 h <sup>1)</sup>			
Rated lamp survival factor at 2,000 h	0.99			
Rated lamp survival factor at 4,000 h	0.99			
Rated lamp survival factor at 6,000 h	0.99			
Rated lamp survival factor at 8,000 h	0.98			
Rated lamp survival factor at 12,000 h	0.95			
Rated lamp survival factor at 16,000 h	0.81			
Rated lamp survival factor at 20,000 h	0.50			
Operation mode LLMF/LSF	HF			
Lifespan	20000 h <sup>1)</sup>			

 $^{1)}$  With preheat ECG

### Additional product data

Base (standard designation)	G24q-3
Lamp mercury content	2.5 mg
Appropriate disposal acc. to WEEE	Yes

### Capabilities


### **Certificates & standards**

Energy efficiency class	A
Energy consumption	29 kWh/1000h

### **Country specific categorizations**

11 605	FEOU 26/027 /D/ C24- 7
ILCOS	FSQH-26/827-/P/-G24q-3

### **Light Distribution**



### Spectral power distribution




Guarantee

Equipment / Accessories

- Suitable for operation on electronic control gear

### Safety advice

In case of lamp breakage: www.osram.com/brokenlamp



Circuit diagram

Circuit diagram

#### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300012230	DULUX D/E 26 W/827	Shipping carton box 10	176 mm x 194 mm x 98 mm	3.35 dm³	665.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

#### References / Links

For more information on QUICKTRONIC electronic control gear go to

www.osram.com/QUICKTRONIC

#### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

# DULUX D/E 26 W/827

# OSRAM DULUX D/E | CFLni, 2 tubes, with 4-pin base for ECG operation

Product name	Product name ECG	EAN	Nominal current	Nominal wattage + Power loss	Luminous flux at 25 °C	Number of lighting outlets
DULUX D/E 26W/827 G24Q-3	QT-ECO 1x26/220-240 S	4008321065971	0.18 A	23.50 W	1600 lm	1
	QT-ECO T/E 2x26/220-240	4050300804002	0.25 A	53.00 W	3500 lm	2
	QTi DALI-T/E 1x18-57 DIM	4008321060808	0.13 A	29.00 W	1800 lm	1
	QTi DALI-T/E 2x18-42 DIM	4008321060822	0.25 A	56.00 W	2*1800 lm	2
	QTi-T/E 1x18-57 DIM	4008321060860	0.13 A	29.00 W	1800 lm	1
	QTi-T/E 2x18-42 DIM	4008321060846	0.25 A	56.00 W	2*1800 lm	2
	QT-M 2x26-42/220-240 S	4008321110022	0.23 A	54.00 W	2*1800 lm	2
	QTP-M 1x26-42	4008321329134	0.12 A	27.00 W	1750 lm	1
	QTP-M 2x26-32	4008321329158	0.24 A	53.00 W	2*1750 lm	2
	QTP-T/E 1x26-42, (2x26)	4008321537089	0.13 A	28.00 W	1750 lm	1
	QTP-T/E (1x26-42), 2x26	4008321537089	0.24 A	54.00 W	2*1750 lm	2