

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 32_N-50-0-1/133_N



Description

Adaptor plug/plug

Interface standards
IEC 60169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

| | | |
|--------------------------|-------------|-------------|
| Impedance | 50 Ω | |
| Interface frequency max. | 11 GHz | |
| Frequency range | DC to 9 GHz | 9 to 12 GHz |
| Return loss | ≥ dB | ≥ dB |

Mechanical Data

Weight 0.0557 kg

Environmental Data

Operating Temperature -65 °C to 165 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

| | |
|----------------|-----------------------|
| Centre contact | Brass |
| Outer contact | Brass |
| Body | Brass |
| Insulator | |
| Coupling nut | Brass |
| Gasket | MVQ (Silicone Rubber) |

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Catalogue drawing DCA-00013682

Ordering Information

Single package 32_N-50-0-1/133_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions