

Max. 28 m<sup>3</sup>/h

## DC centrifugal fans

□ 76 x 27 mm



- **Material:** Scroll housing: GRP<sup>1)</sup>  
Impeller: GRP<sup>1)</sup>
- **Direction of air flow:** Axial: Intake,  
Centrifugal: Exhaust
- **Connection:** via single wires AWG 26, TR 64
- **Highlights:** Forward-curved impeller
- **Weight:** 75 g


- **Possible special versions:**  
(See chapter DC fans - specials)
  - Speed signal
  - Go- / NoGo alarm
  - Alarm with speed limit
  - External temperature sensor
  - Internal temperature sensor
  - PWM control input
  - Analog control input
  - Moisture protection

1) Fiberglass-reinforced plastic

Series RL 48

Nominal data		Air flow m <sup>3</sup> /h	Air flow cfm	Nominal voltage		Voltage range	Sound power level Sintec sleeve bearings Ball bearings	Power consumption	Nominal speed	Temperature range	Hours	Hours	Curve
Type		m <sup>3</sup> /h	cfm	VDC	VDC	Bel(A)	□ / ■	Watts	rpm <sup>-1</sup>	°C			DC fans - specials
RL 48-19/12 ML		22	12.9	12	12	8...15	5.3	■	5.0	3 500	-20...+70	70 000 / 35 000	117 500 ①
RL 48-19/12		28	16.5	12	12	8...13.5	5.7	■	4.6	4 400	-20...+70	60 000 / 30 000	102 500 ②
RL 48-19/14 ML		22	12.9	24	24	18...28	5.3	■	5.0	3 500	-20...+70	70 000 / 35 000	117 500 ①
RL 48-19/14		28	16.5	24	24	18...26.4	5.7	■	4.4	4 400	-20...+70	60 000 / 30 000	102 500 ②

Subject to change



Air performance measured according to: ISO 5801.  
Installation category A, without contact protection.  
Noise: Total sound power level L<sub>WA</sub> ISO 103002  
measured on a hemisphere with a radius of 2 m.  
Sound pressure level L<sub>pA</sub> measured at 1 m distance from  
fan axis.  
The values given are applicable only under the specified  
measuring conditions and may differ depending on the  
installation conditions.  
In the event of deviation from the standard configuration,  
the parameters must be checked after installation!  
For detailed information see  
<http://www.ebmpapst.com/general conditions>

