


Flush pressure sensor with display

PI-2,5-REA01-MFRKG/US/ /P



1 alphanumeric display 4-digit

2 status LEDs

3 programming button

4 G 1 sealing cone external thread

Attention: The unit must only be installed in a process connection for G1 sealing cone. The G1A sealing cone of the unit is only suited for adapters with metal end stop.

 ACS CRN c^{UL}_{us} LISTED


EC 1935/2004 EHEDG Certified



IO-Link

Product characteristics

Output signal	switching signal; analogue signal; IO-Link; (configurable)			
Measuring range	-0.124...2.5 bar	-124...2500 mbar	-1.8...36.27 psi	-12.4...250 kPa
Process connection	threaded connection G 1 external thread sealing cone			

Application

Special feature	Gold-plated contacts			
Application	food and beverage industry			
Media	viscous media and liquids with suspended particles; liquids and gases			
Medium temperature [°C]		-25...125; (145 max. 1h)		
Pressure rating	20 bar	290 psi	2000 kPa	
Min. bursting pressure	50 bar	725 psi	5000 kPa	
Vacuum resistance [mbar]		-1000		
Type of pressure	relative pressure			
MAWP (for applications according to CRN) [bar]	20			

PI2896



Flush pressure sensor with display

PI-2,5-REA01-MFRKG/US/ /P

Electrical data		
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Integrated watchdog		yes
2-wire		
Operating voltage	[V]	20...32 DC
Current consumption	[mA]	3.6...21
Power-on delay time	[s]	1
3-wire		
Operating voltage	[V]	18...32 DC
Current consumption	[mA]	< 45
Power-on delay time	[s]	0.5
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; IO-Link; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Number of analogue outputs		1
Analogue current output	[mA]	4...20, invertible; (scalable)
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
2-wire		
Max. load	[Ω]	300
3-wire		
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	125
Max. load	[Ω]	(Ub - 10 V) / 20 mA

Flush pressure sensor with display

PI-2.5-REA01-MFRKG/US/ /P

Measuring/setting range				
Measuring range		-0.124...2.5 bar	-124...2500 mbar	-1.8...36.27 psi
Set point SP		-0.12...2.5 bar	-1.74...36.27 psi	-12...250 kPa
Reset point rP		-0.124...2.496 bar	-1.8...36.21 psi	-12.4...249.6 kPa
Analogue start point		-0.124...1.88 bar	-1.8...27.27 psi	-12.4...188 kPa
Analogue end point		0.5...2.5 bar	7.26...36.27 psi	50...250 kPa
In steps of		0.002 bar	0.03 psi	0.2 kPa
			SP1 = 0.624 bar	rP1 = 0.574 bar
Factory setting			SP2 = 1.874 bar	rP2 = 1.824 bar
			ASP = 0.000 bar	AEP = 2.500 bar
Accuracy / deviations				
Switch point accuracy	[% of the span]		< ± 0,2; (Turn down 1:1)	
Repeatability	[% of the span]		< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation	[% of the span]		< ± 0,2; (Turn down 1:1 linearity, incl. hysteresis and repeatability limit value setting to DIN 16086)	
Linearity deviation	[% of the span]		< ± 0,15; (Turn down 1:1)	
Hysteresis deviation	[% of the span]		< ± 0,15; (Turn down 1:1)	
Long-term stability	[% of the span]		< ± 0,1; (Turn down 1:1; per year)	
Temperature coefficient zero point	[% of the span / 10 K]		< ± 0,05; (0...70 °C)	
Temperature coefficient span	[% of the span / 10 K]		< ± 0,15; (0...70 °C)	
Response times				
Damping for the switching output dAP	[s]		0...30	
Damping for the analogue output dAA	[s]		0.01...99.99	
2-wire				
Step response time analogue output	[ms]		45	
3-wire				
Min. response time of switching output (dAP)	[ms]		3	
Step response time analogue output	[ms]		7	

PI2896

Flush pressure sensor with display

PI-2,5-REA01-MFRKG/US/ /P



Interfaces				
Communication interface		IO-Link		
Transmission type		COM2 (38,4 kBaud)		
IO-Link revision		1.0		
IO-Link device ID		159 d / 00 00 9F h		
Profiles		no profile		
SIO mode		yes		
Required master port type		A		
Process data analogue		1		
Process data binary		2		
Min. process cycle time	[ms]	2.3		
Operating conditions				
Ambient temperature	[°C]	-25...80		
Storage temperature	[°C]	-40...100		
Protection		IP 67; IP 68; IP 69K		
Tests / approvals				
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD		
	EN 61000-4-3 HF radiated	10 V/m		
	EN 61000-4-4 Burst	2 kV		
	EN 61000-4-5 Surge	0,5/1 kV		
	EN 61000-4-6 HF conducted	10 V		
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)		
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)		
MTTF	[years]	148.85		
Note on approval	factory certificate available as download at www.factory-certificate.ifm			
Mechanical data				
Weight	[g]	378		
Materials	stainless steel (1.4404 / 316L); FKM; PTFE; PBT; PEI; PFA			
Materials (wetted parts)	ceramics (99.9 % Al2O3); PTFE; stainless steel (1.4435 / 316L); surface characteristics: Ra < 0,4 / Rz 4			
Min. pressure cycles	100 million			
Process connection	threaded connection G 1 external thread sealing cone			
Displays / operating elements				
Display	Display unit	LED, green		
	switching status	LED, yellow		
	function display	alphanumeric display, 4-digit		
	measured values	alphanumeric display, 4-digit		
Display unit	bar; kPa; psi; inH2O; mWS; % of the span			
Remarks				
Remarks	Attention: The unit must only be installed in a process connection for G1 sealing cone.			
	The G1A sealing cone of the unit is only suited for adapters with metal end stop.			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M12; Contacts: gold-plated				


Flush pressure sensor with display

PI-2,5-REA01-MFRKG/US/ /P




Connection


(1)



(2)



(3)



- | | |
|------|--|
| 1 | connection for 2-wire operation |
| 2 | connection for 3-wire operation : |
| OUT1 | switching output |
| OUT2 | switching output |
| | analogue output |
| 3 | connection for IO-Link parameter setting (P = communication via IO-Link) |