



Features:

- Multilayer fabrication technology.
- -55°C to 125°C operating temperature range.
- \bullet Operating voltage range $V_{M\ (DC)}$ at 5.5V to 85V.
 - Able to withstand ESD test of IEC-61000-4-2.
- Bi-directional clamping characteristic.

Applications:

Protection of cellular phones, PDA, High speed data line.....etc.


ESD protection for components sensitive to IEC 61000-4-2, provides circuit board transient voltage protection for transistors. Protection of video and audio ports.

Electrical Data

Item	General Specification
Continuous Rating: Steady state applied voltage: DC Voltage range (VM _{DC}) AC Voltage range (VM _{DC RMS})	5.5V to 85V 4V to 60V
Transient Rating: Non-Repetitive surge current (8/20 μ S) Non-Repetitive surge energy, 10/1000 μ S waveform, (W _{TM}) Operating ambient temperature range (T _A) Storage temperature range (T _{STG}) Temperature coefficient (α V) of clamping voltage (V _c) at specified test current	20A to 100A 0.05J to 1.0J -55°C to 125°C -55°C to 150°C <0.01%/°C







Dimensions

Size	MCV0402	MCV0603	MCV0805	MCV1206
L	1.00 ±0.10	1.60 ±0.15	2.00 ±0.20	3.20 ±0.20
W	0.50 ±0.10	0.80 ±0.15	1.25 ±0.20	1.60 ±0.20
Т	0.50 ±0.10	0.80 ±0.15	0.80 ±0.20	0.80 ±0.10mm* 1.10 ±0.20mm**
T _S	0.25 ±0.15	0.35 ±0.15	0.50 ±0.20	0.65 ±0.25

Dimensions : Millimetres

Terminal electrode: Ni / Sn electrode.

Note: * means MCV1206 5.5V dc to 22V dc items ** means MCV1206 26V dc to 85V dc items

Device Rating and Specifications

	Maximum Ratings Specifications									
Maximum Continuous Working Voltage		ntinuous Repetitive Surge Current Surge at Specified No.		Nominal Voltage at 1mA (DC) Current		Typical Capacitance at 1KHz	Part Number			
V _{M (DC)}	V _{M (AC)}	I _{TM}	W _{TM}	v _c	V _{N (DC)} V _{N (DC)} Minimum Maximum		С			
(V)	(V)	(A)	(J)	(V)	(V)	(V)	(pF)			
5.5	4	20	0.05	20 at 1A	8.0	11.0	295	MCV0402M050AGT		
9	6	20	0.05	23 at 1A	10.2	13.8	190	MCV0402M090AGT		
11	8	20	0.05	25 at 1A	12.75	17.25	160	MCV0402M110AGT		
14	11	20	0.05	30 at 1A	15.3	20.7	135	MCV0402M140AGT		
18	14	20	0.05	40 at 1A	21.6	26.4	93	MCV0402M180AGT		
5.5	4	30	0.1	20 at 1A	8.0	11.0	800	MCV0603M050AGT		
9	6	30	0.1	23 at 1A	10.2	13.8	680	MCV0603M090AGT		
14	11	30	0.1	30 at 1A	15.3	20.7	350	MCV0603M140AGT		
18	14	30	0.1	39 at 1A	21.6	26.4	270	MCV0603M180AGT		
26	20	30	0.1	54 at 1A	29.7	36.3	200	MCV0603M260AGT		

http://www.farnell.com http://www.newark.com http://www.cpc.co.uk





Device Rating and Specifications

Maximum Ratings						Specificati	ons	
Maximum Continuous		Maximum Non- Repetitive	Repetitive Clamping Voltage	Nominal Voltage at		Typical Capacitance		
Work Volta		Surge Current (8/20μS)	Energy (10/1000μS)	at Specified Current (8/20μS)	1mA (DC) Current		1mA (DC) Current at 1KHz	
V _{M (DC)}	V _{M (AC)}	I _{TM}	W _{TM}	v _c	V _{N (DC)} Minimum	V _{N (DC)} V _{N (DC)} Minimum Maximum		
(V)	(V)	(A)	(J)	(V)	(V)	(V)	(pF)	
30	25	30	0.1	65 at 1A	35.1	42.9	120	MCV0603M300AGT
38	30	30	0.1	77 at 1A	42.3	51.7	100	MCV0603M380AGT
5.5	4	80	0.1	20 at 1A	8.0	11.0	1600	MCV0805M050AGT
9	6	80	0.1	23 at 1A	10.2	13.8	1180	MCV0805M090AGT
18	14	100	0.2	39 at 1A	21.6	26.4	550	MCV0805M180AGT
22	17	100	0.2	44 at 1A	24.3	29.7	400	MCV0805M220AGT
26	20	100	0.3	54 at 1A	29.7	36.3	350	MCV0805M260AGT
30	25	100	0.3	65 at 1A	35.1	42.9	310	MCV0805M300AGT
38	30	100	0.3	77 at 1A	42.3	51.7	280	MCV0805M380AGT
45	35	80	0.3	90 at 1A	50.4	61.6	195	MCV0805M450AGT
5.5	4	100	0.2	20 at 1A	8.0	11.0	3200	MCV1206M050AGT
14	11	100	0.3	30 at 1A	15.3	20.7	1150	MCV1206M140AGT
18	14	100	0.3	38 at 1A	21.6	26.4	900	MCV1206M180AGT
22	17	100	0.4	44 at 1A	24.3	29.7	840	MCV1206M220AGT
26	20	100	0.5	54 at 1A	29.7	36.3	490	MCV1206M260AGT
30	25	100	0.6	65 at 1A	35.1	42.9	440	MCV1206M300AGT
38	30	100	0.7	77 at 1A	42.3	51.7	400	MCV1206M380AGT
45	35	100	0.8	90 at 1A	50.4	61.6	310	MCV1206M450AGT
56	40	100	1.0	110 at 1A	61.2	74.8	280	MCV1206M560AGT
65	50	100	0.5	135 at 1A	73.8	90.2	240	MCV1206M650AGT
85	60	100	0.6	165 at 1A	90.0	110	160	MCV1206M850AGT

Standard Testing Condition

Unless otherwise specified

Temperature : 15 to 35°C.

Humidity : 25%RH to 85%RH.

Atmospheric pressure : 86kPa to 106kPa.

http://www.farnell.com http://www.newark.com http://www.cpc.co.uk





Specifications

Test Item		Specification			
High temperature storage		25 ±3°C for 1000 easurement to be	ΔV at 1mA <10%		
Low temperature storage		0 ±3°C for 1000 h easurement to be	ours made after keeping at room	temperature for 24 ±2 hou	S ΔV at 1mA <10%
Humidity storage			RH for 500 hours made after keeping at room	temperature for 24 ±2 hou	ΔV at 1mA <10%
		Times: 5 cyc	les		
		Step	Temperature (°C)	Time (Minimum)	
		1	-55 ±3	30 ±3	
Temperature cycles		2	Room temperature	2 to 3	ΔV at 1mA <10%
		3	+125 ±3°C	30 ±2	
		4	Room temperature	2 to 3	
	Me	asurement to be r	made after keeping at room t	emperature for 24 ±2 hours	
Mechanical Reliability					
Solderability	So Im Im	Minimum 90% electrode shall be covered with sold ΔV at 1mA <10%			
Resistance to soldering heat	Pr Sc Im M	Disappearance of electrode due to immersion into solder shall not exceed 25% of edges of each electrode			
	30		and applied ION (1Kgf) for 10 seconds SN (0.5Kgf) for 10 seconds		
			Chip varistor		
Adhesive Strength of Termination			No visible damag		
Vibration	F	No visible damag			
Bending Test	ŗ	No visible damag ΔV at 1mA <10%			


http://www.farnell.com http://www.newark.com http://www.cpc.co.uk






Soldering Condition

Typical examples of soldering processes that provide reliable joints without any damage are given in figure below:



Infrared Soldering Profile


Ordering Code





Packaging

Paper Tape Specifications (Unit: mm) and Packaging Quantity




Α	В	E	F	ØD	Part Number
1.12 ±0.03	0.62 ±0.03	1.75 ±0.05	3.50 ±0.05	1.55 ±0.05	MCV0402
1.80 ±0.05	0.95 ±0.05	1.75 ±0.05	3.50 ±0.05	1.55 ±0.05	MCV0603
2.25 ±0.05	1.45 ±0.05	1.75 ±0.05	3.50 ±0.05	1.55 ±0.05	MCV0805
3.50 ±0.05	1.88 ±0.05	1.75 ±0.05	3.50 ±0.05	1.55 ±0.05	MCV1206

P ₀	P ₁	Т	w	Quantity/Reel	Part Number
4.00 ±0.10	2.00 ±0.10	0.60 ±0.03	8.00 ±0.20	10K Pieces	MCV0402
4.00 ±0.10	2.00 ±0.10	0.87 ±0.05	8.00 ±0.20	4K Pieces	MCV0603
4.00 ±0.10	2.00 ±0.10	1.24 ±0.05	8.00 ±0.20	4K Pieces	MCV1206

[•] Tape Material: Paper tape.

Dimensions : Millimetres

Reel Dimensions



Symbol	Α	В	С	D
Dimension	Ø178.0 ±2.0	Ø60.0 ±1.0	13.0 ±0.2	10.0 ±1.5

Dimensions : Millimetres







Caution of Handling

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment.
- (2) Aerospace equipment.
- (3) Undersea equipment.
- (4) Medical equipment.
- (5) Traffic signal equipment.
- (6) Applications of similar complexity and/or reliability requirements to the applications listed in the above.

Storage Condition

- (1) Products should be used in 6 months from the final date of manufacture which can be confirmed.
- (2) Storage environment condition.
- Products should be storage in the warehouse on the following conditions.
- Temperature : -10 to +40°C.
- Humidity : 30 to 70% relative humidity.
- Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
- Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
- Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be storage under the airtight packaged condition.

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from legigence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.



