

## Pneum. contact metal OD 6 female+valve



Part number	09 14 000 6466
Specification	Pneum. contact metal OD 6 female +valve
HARTING eCatalogue	https://b2b.harting.com/09140006466

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Contacts			
Type of contact	Pneumatic contact			
Description of the contact	With shut-off Straight			
Version				
Gender	Female			
Manufacturing process	Turned contacts			
Technical characteristics				
Limiting temperature	-20 +85 °C Tube outer diameter			
Operating pressure	≤10 bar			
Tube outer diameter	6 mm			
Material properties				
Material (contacts)	Brass			
Material (seal)	HNBR (hydrated NBR)			
RoHS	compliant with exemption			
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight			
ELV status	compliant with exemption			
China RoHS	50			
REACH Annex XVII substances	Not contained			
REACH ANNEX XIV substances	Not contained			

Page 1 / 2 | Creation date 2024-02-24 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



## Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
	Naphthalene

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076			
Commercial data				
Packaging size	10			
Net weight	5 g			
Country of origin	Romania			
European customs tariff number	39269097			
GTIN	5713140162105			
ETIM	EC000796			
eCl@ss	27440204 Contact for industrial connectors			