

## Collection tray for IBC containers

Steel, with grating

### Application:

Prescribed storage of IBC containers and drums, for flammable liquids in GHS categories 1-3 and liquids which pose a hazard to water in GHS categories 1-4.

### Execution:

- 3-mm thick welded sheet steel structure
- 100 mm ground clearance
- With galvanised grating (carrying capacity 1000 kg/m<sup>2</sup>)
- declaration of compliance (ÜHP) pursuant to StawaR



<b>Art. no.</b>	<b>50060 286</b>
<b>Collection volume</b>	1000 l
<b>Max. number of 200-litre containers</b>	10 PCS
<b>Max. number of 1000-litre containers (IBC)</b>	2 PCS
<b>Length</b>	2690 mm
<b>Width</b>	1650 mm
<b>Height</b>	375 mm
<b>For liquids hazardous to water GHS 1-4</b>	Yes
<b>For flammable liquids GHS 1-3</b>	Yes
<b>Declaration of conformity in acc. with StawaR</b>	Yes
<b>With grating</b>	Yes
<b>With bottling attachment</b>	No
<b>Material</b>	Sheet steel
<b>Surface</b>	Lacquered
<b>Colour</b>	Optional
<b>Gross Weight</b>	274.000 kg
<b>Product Group</b>	5AI