UL1061 Style Stranded Hook-Up Wire








This stranded Hook-Up Wire meets the specifications of UL AWM/Style 1061 - 80°C / 300V. UL recognized (UL file no. E352035).

Specifications

Conductor Material	: Stranded Tinned Copper
Insulator Material	: SR PVC
Rated Temperature	: 80°C
Rated Voltage	: 300V
Cable Length	: Available in 305m Reel or in per metre length

Diagram





Marking

E352035 AWM **** **AWG ***C ***V VW-1 NEWARK CORP C AWM **AWG I A ***C ***V FT-1 Rated Voltage



	Rated Voltage
	Rated Temperature
└─ AWG-No	

AWG	Construction # Strands/Strand Size (mm)	Conductor Diameter (mm)	Insulation Diameter (mm)	Conductor Resistance 20°C (Ω/kM)	Insulation Colour	Part Number
	19 24/0.19	4.24	1.0	22.2	Black	PP002567
					Brown	PP002569
					Red	PP002572
18					Yellow	PP002574
18 34/0.18	1.21	1.8	23.2	Green/Yellow	PP002570	
					Blue	PP002568
					Grey	PP002571
					White	PP002573
20 21/0.18	0.95	1.5	36.7	Black	PP002575	
				Red	PP002579	
				Yellow	PP002582	
				Green/Yellow	PP002577	

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk

pro-**Power**



AWG	Construction # Strands/Strand Size (mm)	Conductor Diameter (mm)	Insulation Diameter (mm)	Conductor Resistance 20°C (Ω/kM)	Insulation Colour	Part Number
20		0.95	1.5	36.7	Blue	PP002576
	21/0.18				Purple	PP002580
20	21/0.10				Grey	PP002578
					White	PP002581
					Black	PP002583
22 17/0.16					Brown	PP002585
					Red	PP002589
			4.05		Orange	PP002588
	17/0 16	0.76		59.4	Yellow	PP002592
	0.76	1.25	59.4	Green	PP002586	
					Blue	PP002584
					Purple	PP002590
					Grey	PP002587
					White	PP002591
		0.61	1.15	94.2	Black	PP002593
					Brown	PP002366
					Red	PP002598
24 11/0.16					Orange	PP002597
	11/0 16				Yellow	PP002601
	11/0.10				Green	PP002595
					Blue	PP002594
					Purple	PP002599
					Grey	PP002596
					White	PP002600
		0.49		150	Black	PP002602
			1		Red	PP002368
26	7/0.16				Yellow	PP002369
	7/0.16				Blue	PP002367
					Grey	PP002603
					White	PP002604

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk

