

EL Series 105° SMD Ecap

Aluminium Electrolytic Capacitor

multicomp PRO



Features

- Designed for surface mounting on high density circuit board
- Supplied with carrier taping for automatic mounting machine
- Guarantees 2,000 hours at 105°C

Specification Table


Item	Characteristics												
Operating Temperature Range	40°C to 105°C												
Working Voltage Range	6.3 to 50 V												
Capacitance Range	0.1 to 1,000µF												
Capacitance Tolerance	±20% (120 Hz, 20°C)												
Maximum Leakage Current	I ≤ 0.01 CV or 3 (µA) Whichever is greater (after 2 minute)												
Dissipation Factor at 120 Hz, 20°C	W.V.	6.3	10	16	25	35	50						
	Tan δ (Maximum)	0.35	0.3	0.25	0.18	0.16	0.14						
Low Temperature Characteristics (Impedance ratio at 120 Hz)	W.V.	6.3	10	16	25	35	50						
	Z-25°C / Z+20°C	4	3	2	2	2	2						
	Z-40°C / Z+20°C	10	8	6	4	4	4						
Load Life After Application of the Rated Voltage for 2,000 Hours at 105°C	Capacitance change	Within ±25% of initial value											
	Tan δ	Less than 250% of initial specified value											
	Leakage current	Less than specified value											
Shelf Life (at 105°C)	After 1,000 hours no load test, leakage current, capacitance change and tan δ are as same as load life value												
Soldering Heat Resistance	Place terminal side surface on 250°C hot plate for 30 seconds allow test samples be cooled down to room temperature												
	Capacitance change	Within ±10% of initial value											
	Tan δ	Less than Initial specified value											
	Leakage current												

EL Series 105° SMD Ecap

Aluminium Electrolytic Capacitor

multicomp PRO

Diagram of Dimensions



Dimensions : Millimetres

ØD ± 0.5 Maximum	L	a	A ± 0.2	B ± 0.2	C ± 0.2	W	P ± 0.2
4	5.2	0.3	4.3	4.3	1.8	0.5 to 0.8	1
5			5.3	5.3	2.1		1.4
6.3			6.6	6.6	2.4		2.2
8	10.5	0.5	8.3	8.3	2.9	1.1 to 1.4	3.2
10			10.3	10.3	3.2		4.6

Dimensions : Millimetres

Dimensions and Maximum Permissible Ripple Current mA (rms) at 120 Hz, 105°C

W.V µF \	6.3		10		16		25		35		50	
0.1	-	-	-	-	-	-	-	-	-	-	0.7	
0.22	-	-	-	-	-	-	-	-	-	-	1.6	
0.33	-	-	-	-	-	-	-	-	-	-	2.5	
0.47	-	-	-	-	-	-	-	-	-	-	3.5	
1	-	-	-	-	-	-	-	-	-	-	7	
2.2	-	-	-	-	-	-	-	-	-	-	11	
3.3	-	-	-	-	-	-	-	-	-	-	13	
4.7	-	-	-	-	-	-	4 × 5.2	12	4 × 5.2	14	5 × 5.2	19
10	-	-	-	-	4 × 5.2	16	5 × 5.2	22	5 × 5.2	24	6.3 × 5.2	32
22	4 × 5.2	20	5 × 5.2	25	5 × 5.2	28	6.3 × 5.2	38	6.3 × 5.2	40	6.3 × 7.7	60
33	5 × 5.2	28		33	6.3 × 5.2	39		52	6.3 × 7.7	77	8 × 10.5	140
47		34		41		54	6.3 × 7.7	91	8 × 10.5	150		150
100	6.3 × 5.2	66	6.3 × 5.2	60	6.3 × 7.7	95	8 × 10.5	150		160	10 × 10.5	220

Newark.com/multicomp-pro

Farnell.com/multicomp-pro

Element14.com/multicomp-pro

multicomp PRO

EL Series 105° SMD Ecap

Aluminium Electrolytic Capacitor

multicomp PRO

Dimensions and Maximum Permissible Ripple Current mA (rms) at 120 Hz, 105°C

W.V μF	6.3		10		16		25		35		50	
220	6.3 × 7.7	105	8 × 10.5	175	8 × 10.5	175	8 × 10.5	195	10 × 10.5	290	-	-
330		195		195		210	10 × 10.5	290	-	-	-	-
470	8 × 10.5	210		210	10 × 10.5	290	-	-	-	-	-	-
680	-	-		300	-	-	-	-	-	-	-	-
1,000	10 × 10.5	300	-	-	-	-	-	-	-	-	-	-

Part Number Table

Description	Part Number	Description	Part Number
Capacitor, Case B, 22μF, 6.3V	MCEEL6V3226M4X5.2	Capacitor, Case G, 47μF, 25V	MCEEL25V476M6.3X7.7
Capacitor, Case D, 33μF, 6.3V	MCEEL6V3336M5X5.2	Capacitor, Case H, 220μF, 25V	MCEEL25V227M8X10.5
Capacitor, Case D, 47μF, 6.3V	MCEEL6V3476M5X5.2	Capacitor, Case J, 330μF, 25V	MCEEL25V337M10X10.5
Capacitor, Case G, 220μF, 6.3V	MCEEL6V3227M6.3X7.7	Capacitor, Case D, 10μF, 35V	MCEEL35V106M5X5.2
Capacitor, Case H, 330μF, 6.3V	MCEEL6V3337M8X10.5	Capacitor, Case G, 33μF, 35V	MCEEL35V336M6.3X7.7
Capacitor, Case H, 470μF, 6.3V	MCEEL6V3477M8X10.5	Capacitor, Case H, 47μF, 35V	MCEEL35V476M8X10.5
Capacitor, Case J, 1000μF, 6.3V	MCEEL6V3108M10X10.5	Capacitor, Case H, 100μF, 35V	MCEEL35V107M8X10.5
Capacitor, Case D, 22μF, 10V	MCEEL10V226M5X5.2	Capacitor, Case J, 220μF, 35V	MCEEL35V227M10X10.5
Capacitor, Case D, 33μF, 10V	MCEEL10V336M5X5.2	Capacitor, Case B, 2.2μF, 50V	MCEEL50V225M4X5.2
Capacitor, Case E, 47μF, 10V	MCEEL10V476M6.3X5.2	Capacitor, Case B, 3.3μF, 50V	MCEEL50V335M4X5.2
Capacitor, Case E, 100μF, 10V	MCEEL10V107M6.3X5.2	Capacitor, Case G, 22μF, 50V	MCEEL50V226M6.3X7.7
Capacitor, Case H, 330μF, 10V	MCEEL10V337M8X10.5	Capacitor, Case H, 33μF, 50V	MCEEL50V336M8X10.5
Capacitor, Case H, 470μF, 10V	MCEEL10V477M8X10.5	Capacitor, Case E, 100μF, 6.3V	MCEEL6V3107M6.3X5.2
Capacitor, Case D, 22μF, 16V	MCEEL16V226M5X5.2	Capacitor, Case H, 220μF, 10V	MCEEL10V227M8X10.5
Capacitor, Case E, 33μF, 16V	MCEEL16V336M6.3X5.2	Capacitor, Case B, 10μF, 16V	MCEEL16V106M4X5.2
Capacitor, Case G, 100μF, 16V	MCEEL16V107M6.3X7.7	Capacitor, Case E, 47μF, 16V	MCEEL16V476M6.3X5.2
Capacitor, Case H, 220μF, 16V	MCEEL16V227M8X10.5	Capacitor, Case H, 100μF, 25V	MCEEL25V107M8X10.5
Capacitor, Case H, 330μF, 16V	MCEEL16V337M8X10.5	Capacitor, Case B, 4.7μF, 35V	MCEEL35V475M4X5.2
Capacitor, Case J, 470μF, 16V	MCEEL16V477M10X10.5	Capacitor, Case E, 22μF, 35V	MCEEL35V226M6.3X5.2
Capacitor, Case B, 4.7μF, 25V	MCEEL25V475M4X5.2	Capacitor, Case B, 1μF, 50V	MCEEL50V105M4X5.2
Capacitor, Case D, 10μF, 25V	MCEEL25V106M5X5.2	Capacitor, Case D, 4.7μF, 50V	MCEEL50V475M5X5.2
Capacitor, Case E, 22μF, 25V	MCEEL25V226M6.3X5.2	Capacitor, Case E, 10μF, 50V	MCEEL50V106M6.3X5.2
Capacitor, Case E, 33μF, 25V	MCEEL25V336M6.3X5.2	Capacitor, Case H, 47μF, 50V	MCEEL50V476M8X10.5
		Capacitor, Case J, 100μF, 50V	MCEEL50V107M10X10.5

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.