

## Wet and dry vacuum cleaner NSG UCLEAN ARDL-1432 EHP

Power consumption 1400 watt

starmix

### Application:

For assembly work at the construction site (wet/dry) (concrete, stone, cement) and working with electric tools in the workshop (wood, paints, varnishes) with non-hazardous dusts, at normal dust development.

### Execution:

- Single-stage high-speed motors with high-speed turbine and bypass cooling
- Extremely robust folding filter cartridge (IFA (BIA) tested for dust class M)
- Impact-resistant plastic container – resists all common fats and alkalis
- Pneumatic water level detection
- Filter is cleaned automatically during breaks in work
- With additional blow-out function

### Delivery:

With 3.2-m suction hose, 1x handle tube (made of plastic with admixed air slider), 2x suction tubes (made of plastic, 50 cm each), 1x joint nozzle, 1x rubber nozzle, 1x floor nozzle BG Bau



<b>Art. no.</b>	<b>75534 051</b>
<b>Brand</b>	STARMIX
<b>Manufacturer Part Number</b>	016344
<b>Model</b>	uClean ARDL-1432 EHP
<b>Power input</b>	1400 W
<b>Max. air delivery volume</b>	4140 l/min
<b>Material of bins</b>	Plastic
<b>Underpressure</b>	259 mbar
<b>Bin capacity</b>	32 l
<b>Sound-pressure level</b>	72
<b>Weight</b>	9.6 kg
<b>Cable length</b>	8 m
<b>Filter cleaning</b>	Fully automated
<b>With device connector</b>	Yes
<b>With antistatic system</b>	Yes
<b>With automatic shut off</b>	Yes
<b>With accessory tray</b>	Yes
<b>With soft start</b>	Yes
<b>Length x width x height</b>	430 x 390 x 640 mm
<b>With speed control</b>	Yes
<b>Inner hose diameter</b>	35 mm
<b>Hose length</b>	3.2 m
<b>Nominal voltage</b>	230 V
<b>Gross Weight</b>	12.000 kg
<b>Product Group</b>	759

### EAN

4011240016344