



NH-FUSE-BASE WITH MICROSWITCH 250A 1000V  
SIZE 1 FOR PHOTOVOLTAIC APPLICATION

Model		
product brand name		SENTRON
<b>Design of the product</b>		3NH LV HRC fuse bases
General technical data		
<b>Number of poles</b>		1
<b>Size of fuse system / acc. to DIN EN 60269-1</b>		NH1
Electricity		
rated current $I_n$ / IEC, DIN/VDE / at 40 Cel	A	230
Current / with AC / Rated value	A	250
Product details		
Product component / Swivel mechanism		Yes
Connections		
Tightening torque / with screw-type terminals / maximum	N·m	20
<b>Type of electrical connection</b> • for main current circuit		for mounting on mounting plate flat connector
Mechanical Design		
<b>Height</b>	mm	318
<b>Depth</b>	mm	156
<b>Mounting type</b>		fixed mounting
Mounting type / bus-mounting		No



#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NH72624KK01>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3NH72624KK01/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NH72624KK01](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NH72624KK01)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015