

Dot laser, blue, 450 nm, 60 mW

E450-60-5(16x25)
Order Number: 70141160

Main Parameters (*)	min	typ	max	Unit
Wavelength	440	450	460	nm
Optical Output Power	50	60	70	mW
Operating Voltage	4	5	6	V DC
Operating Current	100	400	500	mA
Operating Temperature	-20		60	°C
Storage Temperature	-20		80	°C

Main Data

Warranty 1 years

Technical Parameters

Lifetime > 10,000 h
RoHS yes

Optical Parameters

Beam Shape	Dot
Laser Class	3R
Divergence	D - 0.5 mrad
Beam Diameter	15 mm
Operating Distance	10 m
Optics	glass lens AR coated
Laser technology	diode
Focus	collimated

Electrical Parameters

Potential of Housing isolated
Power Supply LFNT-5

Mechanical Parameters

Size	Ø16x25 mm
Material	Brass
Cable length	115 mm
Output Aperture	5 mm
Housing Color	brass
Weight	31.5 g

(*) Over the complete operating temperature range

Features



- Operating Voltage 5 V DC
- Compact size
- Laser Class 3R
- High Power


Picture



Cable color

Ground  black GND
positive  red 4 - 6, typ 5 V DC

Safety Label



Valid Revision

| 09-NOV-2020