



Is Now Part of



**ON Semiconductor®**

To learn more about ON Semiconductor, please visit our website at  
[www.onsemi.com](http://www.onsemi.com)

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at [www.onsemi.com](http://www.onsemi.com). Please email any questions regarding the system integration to [Fairchild\\_questions@onsemi.com](mailto:Fairchild_questions@onsemi.com).

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

# FXLH42245

## Low-Voltage, Dual-Supply, 8-Bit, Signal Translator with Configurable Voltage Supplies, Bushold Data Inputs, 3-State Outputs and 26Ω Series Resistors in the B-Port Outputs

### Features

- Bi-Directional Interface between Two Levels from 1.1V to 3.6V
- Fully Configurable, Inputs Track V<sub>CC</sub> Level
- Non-Preferential Power-up; Either V<sub>CC</sub> May Be Powered-up First
- Outputs Remain in 3-State until Active V<sub>CC</sub> Level is Reached
- Outputs Switch to 3-State if Either V<sub>CC</sub> is at GND
- Bushold on Data Inputs Eliminates the need for External Pull-Up / Pull-Down Resistors
- 26W Output Series Resistors on the B Port to Reduce Line Noise
- Power-Off Protection
- Control Inputs ( $\overline{T/R}$ ,  $\overline{OE}$ ) Levels are Referenced To V<sub>CCA</sub> Voltage
- Packaged in 24-Pin MLP
- ESD Protection Exceeds:
  - 4kV Human Body Model (per JESD22-A114 & Mil Std 883e 3015.7)
  - 8kV Human Body Model I/O to GND (per JESD22-A114 & Mil Std 883e 3015.7)
  - 1kV Charge Device Model (per ESD STM 5.3)
  - 200V Machine Model (per JESD22-A115 & ESD STM5.2)


### Description

The FXLH42245 is a configurable dual-voltage-supply translator designed for bi-directional voltage translation of signals between two voltage levels. The device allows translation between voltages as high as 3.6V to as low as 1.1V. The A port tracks the V<sub>CCA</sub> level and the B port tracks the V<sub>CCB</sub> level. Both ports are designed to accept supply voltage levels from 1.1V to 3.6V. This allows for bi-directional voltage translation over a variety of voltage levels: 1.2V, 1.5V, 1.8V, 2.5V, and 3.3V.

The device remains in 3-state until both V<sub>CCs</sub> reach active levels, allowing either V<sub>CC</sub> to be powered-up first. The device also contains power-down control circuits that place the device in 3-state if either V<sub>CC</sub> is removed.

The Transmit/Receive ( $\overline{T/R}$ ) input determines the direction of data flow through the device. The  $\overline{OE}$  input, when HIGH, disables both the A and B ports by placing them in a 3-state condition. The FXLH42245 is designed with the control pins ( $\overline{T/R}$  and OE) supplied by V<sub>CCA</sub>.

### Ordering Information

Part Number	 Eco Status	Package	Packing Method
FXLH42245MPX	Green	24-Pin Molded Leadless Package (MLP), JEDEC MO-220, 3.5 x 4.5mm	Tape and Reel

 For Fairchild's definition of Eco Status, please visit: [http://www.fairchildsemi.com/company/green/rohs\\_green.html](http://www.fairchildsemi.com/company/green/rohs_green.html).

## Pin Configuration




Figure 1. Pin Configuration (Top Through View)

## Pin Definitions

Pin #	Name	Description
1	V <sub>CCA</sub>	Side-A Power Supply
2	$\overline{T/R}$	Transmit / Receive Input
3, 4, 5, 6, 7, 8, 9, 10	A <sub>0</sub> , A <sub>1</sub> , A <sub>2</sub> , A <sub>3</sub> , A <sub>4</sub> , A <sub>5</sub> , A <sub>6</sub> , A <sub>7</sub>	Side-A Inputs or 3-State Outputs
11, 12, 13	GND	Ground
14, 15, 16, 17, 18, 19, 20, 21	B <sub>7</sub> , B <sub>6</sub> , B <sub>5</sub> , B <sub>4</sub> , B <sub>3</sub> , B <sub>2</sub> , B <sub>1</sub> , B <sub>0</sub>	Side-B Inputs or 3-State Outputs
22	$\overline{OE}$	Output Enable Input
23, 24	V <sub>CCB</sub>	Side-B Power Supply

## Truth Table

Inputs		Description
$\overline{OE}$	$\overline{T/R}$	
LOW Voltage Level	LOW Voltage Level	Bus B Data to Bus A
LOW Voltage Level	HIGH Voltage Level	Bus A Data to Bus B
HIGH Voltage Level	Don't Care	3-State

## Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Conditions	Min.	Max.	Unit
$V_{CCA}$	Supply Voltage		-0.5	4.6	V
$V_{CCB}$			-0.5	4.6	
$V_I$	DC Input Voltage	I/O Port A	-0.5 to $V_{CCA}$	0.5	V
		I/O Port B	-0.5 to $V_{CCB}$	0.5	
		Control Inputs ( $\overline{T/R}$ , $\overline{OE}$ )	-0.5	0.5	
$V_O$	Output Voltage <sup>(1)</sup>	Output 3-State	-0.5	4.6	V
		Output Active ( $A_n$ )	-0.5 to $V_{CCA}$	0.5	
		Output Active ( $B_n$ )	-0.5 to $V_{CCB}$	0.5	
$I_{IK}$	DC Input Diode Current	$V_I < 0V$		-50	mA
$I_{OK}$	DC Output Diode Current	$V_O < 0V$		-50	mA
		$V_O > V_{CC}$		50	
$I_{OH}/I_{OL}$	DC Output Source/Sink Current			$\pm 50$	mA
$I_{CC}$	DC $V_{CC}$ or Ground Current per Supply Pin			$\pm 100$	mA
$T_{STG}$	Storage Temperature Range		-65	+150	$^{\circ}C$
ESD	Electrostatic Discharge Capability	Human Body Model, JESD22-A114, Mil Std 883e 3015.7	I/O to GND	4	kV
				8	
		Charged Device Model, JESD22-C101, STM 5.3		1	V
		Machine Model, JESD22-A115, STM 5.2		200	

**Note:**

1. I/O absolute maximum ratings must be observed.

## Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameter	Conditions	Min.	Max.	Unit	
$V_{CC}$	Power Supply	Operating $V_{CCA}$ or $V_{CCB}$	1.1	3.6	V	
$V_I$	Input Voltage	Port A	0	$V_{CCA}$	V	
		Port B	0	$V_{CCB}$		
		Control Inputs ( $\overline{T/R}$ , $\overline{OE}$ )	0	$V_{CCA}$		
$I_{OH}/I_{OL}$	Output Current	Port A $V_{CCA}$	3.0V to 3.6V		$\pm 24$	mA
			2.3V to 2.7V		$\pm 18$	
			1.65V to 1.95V		$\pm 6$	
			1.40V to 1.65V		$\pm 2$	
			1.1V to 1.4V		$\pm 0.5$	
		Port B $V_{CCB}$ Resistor Outputs	3.0V to 3.6V		$\pm 14$	
			2.3V to 2.7V		$\pm 8$	
			1.65V to 1.95V		$\pm 3$	
			1.40V to 1.65V		$\pm 1$	
			1.1V to 1.4V		$\pm 0.25$	
$T_A$	Operating Temperature, Free Air		-40	+85	$^{\circ}C$	
$\Delta V/\Delta t$	Minimum Input Edge Rate	$V_{CCA/B} = 1.1V$ to 3.6V		10	ns/V	

**Note:**

2. All unused inputs must be held at  $V_{CCI}$  or GND.

### Electrical Characteristics

Symbol	Parameter	Conditions	V <sub>CCI</sub> (V)	V <sub>CC0</sub> (V)	Min.	Max.	Units
V <sub>IH</sub>	HIGH Level Input <sup>(3)</sup>	Data Inputs A <sub>n</sub> , B <sub>n</sub>	2.70 to 3.60	1.1 to 3.6	2.0		V
			2.30 to 2.70		1.6		
			1.65 to 2.30		0.65 x V <sub>CCI</sub>		
			1.40 to 1.65		0.65 x V <sub>CCI</sub>		
			1.10 to 1.40		0.9 x V <sub>CCI</sub>		
		Control Pins $\overline{OE}$ , T/R (Referenced to V <sub>CCA</sub> )	2.70 to 3.6	1.1 to 3.6	2.0		
			2.30 to 2.70		1.6		
			1.65 to 2.30		0.65 x V <sub>CCA</sub>		
			1.40 to 1.65		0.65 x V <sub>CCA</sub>		
			1.10 to 1.40		0.9 x V <sub>CCA</sub>		
V <sub>IL</sub>	LOW Level Input <sup>(3)</sup>	Data Inputs A <sub>n</sub> , B <sub>n</sub>	2.70 to 3.60	1.1 to 3.6		0.8	V
			2.30 to 2.70			0.7	
			1.65 to 2.30			0.35 x V <sub>CCI</sub>	
			1.40 to 1.65			0.35 x V <sub>CCI</sub>	
			1.10 to 1.40			0.10 x V <sub>CCI</sub>	
		Control Pins $\overline{OE}$ , T/R (Referenced to V <sub>CCA</sub> )	2.70 to 3.60	1.1 to 3.6		0.8	
			2.30 to 2.70			0.7	
			1.65 to 2.30			0.35 x V <sub>CCA</sub>	
			1.40 to 1.65			0.35 x V <sub>CCA</sub>	
			1.10 to 1.40			0.10 x V <sub>CCA</sub>	
V <sub>OH</sub>	HIGH Level Output <sup>(4)</sup> B Port	I <sub>OH</sub> = -100μA	1.1 to 3.6	1.1 to 3.6	V <sub>CC0</sub> to 0.2		V
		I <sub>OH</sub> = -6mA	2.7	2.7	2.2		
		I <sub>OH</sub> = -8mA	3.0	3.0	2.4		
		I <sub>OH</sub> = -12mA	3.0	3.0	2.2		
		I <sub>OH</sub> = -4mA	2.3	2.3	2.0		
		I <sub>OH</sub> = -6mA	2.3	2.3	1.8		
		I <sub>OH</sub> = -8mA	2.3	2.3	1.7		
		I <sub>OH</sub> = -3mA	1.65	1.65	1.25		
		I <sub>OH</sub> = -1mA	1.4	1.4	1.05		
		I <sub>OH</sub> = -0.25mA	1.1	1.1	0.75 x V <sub>CC0</sub>		
	HIGH Level Output <sup>(4)</sup> A Port	I <sub>OH</sub> = -100μA	1.1 to 3.6	1.1 to 3.6	V <sub>CC0</sub> to 0.2		
		I <sub>OH</sub> = -12mA	2.7	2.7	2.2		
		I <sub>OH</sub> = -18mA	3.0	3.0	2.4		
		I <sub>OH</sub> = -24mA	3.0	3.0	2.2		
		I <sub>OH</sub> = -6mA	2.3	2.3	2.0		
		I <sub>OH</sub> = -12mA	2.3	2.3	1.8		
		I <sub>OH</sub> = -18mA	2.3	2.3	1.7		
		I <sub>OH</sub> = -6mA	1.65	1.65	1.25		
		I <sub>OH</sub> = -2mA	1.4	1.4	1.05		
		I <sub>OH</sub> = -0.5mA	1.1	1.1	0.75 x V <sub>CC0</sub>		

Continued on the following page

**Electrical Characteristics** (Continued)

Symbol	Parameter	Conditions	V <sub>CCI</sub> (V)	V <sub>CCO</sub> (V)	Min.	Max.	Units
V <sub>OL</sub>	LOW Level Output <sup>(4)</sup> B Port	I <sub>OL</sub> = 100μA	1.1 to 3.6	1.1 to 3.6		0.2	V
		I <sub>OL</sub> = 6mA	2.7	2.7		0.4	
		I <sub>OL</sub> = 8mA	3.0	3.0		0.55	
		I <sub>OL</sub> = 12mA	3.0	3.0		0.80	
		I <sub>OL</sub> = 6mA	2.3	2.3		0.4	
		I <sub>OL</sub> = 8mA	2.3	2.3		0.6	
		I <sub>OL</sub> = 3mA	1.65	1.65		0.3	
		I <sub>OL</sub> = 1mA	1.4	1.4		0.35	
		I <sub>OL</sub> = 0.25mA	1.1	1.1		0.3 x V <sub>CCO</sub>	
	LOW Level Output <sup>(4)</sup> A Port	I <sub>OL</sub> = 100μA	1.1 to 3.6	1.1 to 3.6		0.2	
		I <sub>OL</sub> = 12mA	2.7	2.7		0.4	
		I <sub>OL</sub> = 18mA	3.0	3.0		0.4	
		I <sub>OL</sub> = 24mA	3.0	3.0		0.55	
		I <sub>OL</sub> = 12mA	2.3	2.3		0.4	
		I <sub>OL</sub> = 18mA	2.3	2.3		0.6	
		I <sub>OL</sub> = 6mA	1.65	1.65		0.3	
		I <sub>OL</sub> = 2mA	1.4	1.4		0.35	
		I <sub>OL</sub> = 0.5mA	1.1	1.1		0.3 x V <sub>CCO</sub>	
I <sub>L</sub>	Input Leakage Current, Control Pins	V <sub>I</sub> =V <sub>CCA</sub> or GND	1.1 to 3.6	3.6		±1.0	μA
I <sub>I(HOLD)</sub>	Bushold Input Minimum Drive Current	V <sub>IN</sub> =0.8	3.0	3.0	75		μA
		V <sub>IN</sub> =2.0	3.0	3.0	-75		
		V <sub>IN</sub> =0.7	2.3	2.3	45		
		V <sub>IN</sub> =1.6	2.3	2.3	-45		
		V <sub>IN</sub> =0.57	1.65	1.65	25		
		V <sub>IN</sub> =10.7	1.65	1.65	-25		
		V <sub>IN</sub> =0.49	1.4	1.4	11		
		V <sub>IN</sub> =0.91	1.4	1.4	-11		
		V <sub>IN</sub> =0.11	1.1	1.1	4		
		V <sub>IN</sub> =0.99	1.1	1.1	-4		
I <sub>I(OD)</sub>	Bushold Input Over-Drive Current-to-Current State	Note 5	3.6	3.6	450		μA
		Note 6	3.6	3.6	-450		
		Note 5	2.7	2.7	300		
		Note 6	2.7	2.7	-300		
		Note 5	1.95	1.95	200		
		Note 6	1.95	1.95	-200		
		Note 5	1.6	1.6	120		
		Note 6	1.6	1.6	-120		
		Note 5	1.4	1.4	80		
		Note 6	1.4	1.4	-80		

Continued on the following page

**Electrical Characteristics** (Continued)

Symbol	Parameter	Conditions	V <sub>CCI</sub> (V)	V <sub>CCO</sub> (V)	Min.	Max.	Units
I <sub>OFF</sub>	Power Off Leakage Current	A <sub>n</sub> , V <sub>I</sub> or V <sub>O</sub> =0V to 3.6V	0	3.6		±10	μA
		B <sub>n</sub> , V <sub>I</sub> or V <sub>O</sub> =0V to 3.6V	3.6	0		±10	
I <sub>OZ</sub>	3-State Output Leakage (V <sub>O</sub> , V <sub>CC</sub> or GND V <sub>I</sub> =V <sub>IH</sub> or V <sub>IL</sub> )	A <sub>n</sub> , B <sub>n</sub> , $\overline{OE}$ =V <sub>IH</sub>	3.6	3.6		±10	μA
		B <sub>n</sub> , $\overline{OE}$ = Don't Care <sup>(7)</sup>	0	3.6		±10	
		A <sub>n</sub> , $\overline{OE}$ = Don't Care <sup>(7)</sup>	3.6	0		±10	
I <sub>CCA/B</sub>	Quiescent Supply Current <sup>(8)</sup>	V <sub>I</sub> =V <sub>CCI</sub> or GND; I <sub>O</sub> =0	1.1 to 3.6	1.1 to 3.6		20	μA
I <sub>CCZ</sub>			1.1 to 3.6	1.1 to 3.6		20	
I <sub>CCA</sub>		V <sub>I</sub> =V <sub>CCA</sub> or GND; I <sub>O</sub> =0	0	1.1 to 3.6		-10	
			1.1 to 3.6	0		10	
I <sub>CCB</sub>		V <sub>I</sub> =V <sub>CCB</sub> or GND; I <sub>O</sub> =0	1.1 to 3.6	0		-10	
			0	1.1 to 3.6		10	
ΔI <sub>CCA/B</sub>	Increase in I <sub>CC</sub> per Input; Other Inputs at V <sub>CC</sub> or GND	V <sub>IH</sub> =3.0	3.6	3.6		500	μA

**Notes:**

3. V<sub>CCI</sub> = the V<sub>CC</sub> associated with the data input under test.
4. V<sub>CCO</sub> = the V<sub>CC</sub> associated with the output under test.
5. An external driver must source at least the specified current to switch LOW-to-HIGH.
6. An external driver must source at least the specified current to switch HIGH-to-LOW.
7. Don't care = any valid logic level.
8. Reflects current per supply, V<sub>CCA</sub> or V<sub>CCB</sub>.

## AC Electrical Characteristics

**V<sub>CCA</sub>=3.0V to 3.6V**

Symbol	Parameter	T <sub>A</sub> = -40 to +85°C										Units
		V <sub>CCB</sub> =3.0V to 3.6V		V <sub>CCB</sub> =2.3V to 2.7V		V <sub>CCB</sub> =1.65V to 1.95V		V <sub>CCB</sub> =1.4V to 1.6V		V <sub>CCB</sub> =1.1V to 1.3V		
		Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
t <sub>PLH</sub> , t <sub>PHL</sub>	Propagation Delay A to B	0.5	3.9	0.5	4.5	0.9	5.9	1.0	7.4	1.6	22.0	ns
	Propagation Delay B to A	0.2	3.5	0.2	3.8	0.3	4.0	0.5	4.3	0.8	13.0	
t <sub>PZH</sub> , t <sub>PZL</sub>	Output Enable OE to B	0.7	4.8	0.1	5.1	1.5	6.7	1.5	7.1	2.0	18.0	ns
	Output Enable OE to A	0.5	4.0	0.5	4.0	0.5	4.0	0.5	4.0	0.5	4.0	
t <sub>PHZ</sub> , t <sub>PLZ</sub>	Output Disable OE to B	0.4	4.3	0.4	4.4	0.9	5.2	1.7	6.8	2.0	19.0	ns
	Output Disable OE to A	0.2	3.7	0.2	3.7	0.2	3.7	0.2	3.7	0.2	3.7	

**V<sub>CCA</sub>=2.3V to 2.7V**

Symbol	Parameter	T <sub>A</sub> = -40 to +85°C										Units
		V <sub>CCB</sub> =3.0V to 3.6V		V <sub>CCB</sub> =2.3V to 2.7V		V <sub>CCB</sub> =1.65V to 1.95V		V <sub>CCB</sub> =1.4V to 1.6V		V <sub>CCB</sub> =1.1V to 1.3V		
		Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
t <sub>PLH</sub> , t <sub>PHL</sub>	Propagation Delay A to B	0.5	4.3	0.6	4.8	0.9	6.0	1.0	7.6	1.6	22.0	ns
	Propagation Delay B to A	0.3	3.9	0.4	4.2	0.5	4.5	0.5	4.8	1.0	7.0	
t <sub>PZH</sub> , t <sub>PZL</sub>	Output Enable OE to B	0.8	5.1	1.0	5.5	1.5	6.9	1.5	7.4	2.0	19.0	ns
	Output Enable OE to A	0.6	4.5	0.6	4.5	0.6	4.5	0.6	4.5	0.6	4.5	
t <sub>PHZ</sub> , t <sub>PLZ</sub>	Output Disable OE to B	0.4	4.6	0.4	4.8	0.9	5.3	1.7	7.1	2.0	19.0	ns
	Output Disable OE to A	0.2	4.0	0.2	4.0	0.2	4.0	0.2	4.0	0.2	4.0	

**V<sub>CCA</sub>=1.65V to 1.95V**

Symbol	Parameter	T <sub>A</sub> = -40 to +85°C										Units
		V <sub>CCB</sub> =3.0V to 3.6V		V <sub>CCB</sub> =2.3V to 2.7V		V <sub>CCB</sub> =1.65V to 1.95V		V <sub>CCB</sub> =1.4V to 1.6V		V <sub>CCB</sub> =1.1V to 1.3V		
		Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
t <sub>PLH</sub> , t <sub>PHL</sub>	Propagation Delay A to B	0.5	4.6	0.7	5.1	1.1	6.2	1.1	7.8	1.7	22.0	ns
	Propagation Delay B to A	0.5	5.4	0.5	5.6	0.8	5.7	1.0	6.0	1.2	8.0	
t <sub>PZH</sub> , t <sub>PZL</sub>	Output Enable OE to B	0.8	5.4	1.0	5.9	1.5	7.3	1.5	7.7	2.0	20.0	ns
	Output Enable OE to A	1.0	6.7	1.0	6.7	1.0	6.7	1.0	6.7	1.0	6.7	
t <sub>PHZ</sub> , t <sub>PLZ</sub>	Output Disable OE to B	0.4	4.7	0.4	4.9	1.0	5.4	1.7	7.2	2.0	19.0	ns
	Output Disable OE to A	0.5	5.0	0.5	5.0	0.5	5.0	0.5	5.0	0.5	5.0	



**AC Electrical Characteristics** (Continued)

 $V_{CCA}=1.4V$  to  $1.6V$ 

Symbol	Parameter	$T_A = -40$ to $+85^\circ\text{C}$										Units
		$V_{CCB}=3.0V$ to $3.6V$		$V_{CCB}=2.3V$ to $2.7V$		$V_{CCB}=1.65V$ to $1.95V$		$V_{CCB}=1.4V$ to $1.6V$		$V_{CCB}=1.1V$ to $1.3V$		
		Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
$t_{PLH}, t_{PHL}$	Propagation Delay A to B	0.7	4.8	0.8	5.3	1.2	6.4	1.3	7.9	2.0	22.0	ns
	Propagation Delay B to A	0.6	6.8	0.8	6.9	0.9	7.1	1.0	7.3	1.3	9.5	
$t_{PZH}, t_{PZL}$	Output Enable OE to B	1.1	5.8	1.3	6.3	1.5	7.8	2.0	8.1	2.0	20.0	ns
	Output Enable OE to A	1.0	7.5	1.0	7.5	1.0	7.5	1.0	7.5	1.0	7.5	
$t_{PHZ}, t_{PLZ}$	Output Disable OE to B	0.6	4.8	0.6	5.1	1.1	5.8	2.0	7.7	2.0	18.0	ns
	Output Disable OE to A	1.0	6.0	1.0	6.0	1.0	6.0	1.0	6.0	1.0	6.0	

 $V_{CCA}=1.1V$  to  $1.3V$ 

Symbol	Parameter	$T_A = -40$ to $+85^\circ\text{C}$										Units
		$V_{CCB}=3.0V$ to $3.6V$		$V_{CCB}=2.3V$ to $2.7V$		$V_{CCB}=1.65V$ to $1.95V$		$V_{CCB}=1.4V$ to $1.6V$		$V_{CCB}=1.1V$ to $1.3V$		
		Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
$t_{PLH}, t_{PHL}$	Propagation Delay A to B	1.0	13.8	1.0	7.8	1.0	8.4	1.0	10.4	2.0	24.0	ns
	Propagation Delay B to A	1.4	22.0	1.4	22.0	1.5	22.0	1.5	22.0	2.0	24.0	
$t_{PZH}, t_{PZL}$	Output Enable OE to B	1.5	12.6	1.5	9.6	1.5	10.6	2.0	11.6	2.0	24.0	ns
	Output Enable OE to A	2.0	22.0	2.0	22.0	2.0	22.0	2.0	22.0	2.0	22.0	
$t_{PHZ}, t_{PLZ}$	Output Disable OE to B	1.2	15.0	0.9	7.6	1.2	8.6	2.0	10.6	3.0	21.0	ns
	Output Disable OE to A	2.0	15.0	2.0	12.0	2.0	12.0	2.0	12.0	2.0	12.0	

**Capacitance**

Symbol	Parameter	Conditions	$T_A = +25^\circ\text{C}$	Units
			Typical	
$C_{IN}$	Input Capacitance Control Pins (OE, T/R)	$V_{CCA}=V_{CCB}=3.3V, V_I=0V$ or $V_{CCA/B}$	4	pF
$C_{I/O}$	Input/Output Capacitance $A_n, B_n$ Port	$V_{CCA}=V_{CCB}=3.3V, V_I=0V$ or $V_{CCA/B}$	5	pF
$C_{PD}$	Power Dissipation Capacitance	$V_{CCA}=V_{CCB}=3.3V, V_I=0V$ or $V_{CC}, f=10\text{MHz}$	20	pF

## AC Loadings and Waveforms





Figure 2. AC Test Circuit

Test	Switch
$t_{PLH}, t_{PHL}$	Open
$t_{PLZ}, t_{PZL}$	$V_{CC0} \cdot 2$ at $V_{CC0}=3.3 \pm 0.3V, 2.5V \pm 0.2V, 1.8V \pm 0.15V, 1.5V \pm 0.1V, 1.2V \pm 0.1V$
$t_{PHZ}, t_{PZH}$	GND

Table 1. AC Load Table


$V_{CC0}$	$C_L$	$R_L$	$R_{tr1}$
$1.2V \pm 0.1V$	15pF	2k $\Omega$	2k $\Omega$
$1.5V \pm 0.1V$	15pF	2k $\Omega$	2k $\Omega$
$1.8V \pm 0.15V$	30pF	500 $\Omega$	500 $\Omega$
$2.5V \pm 0.2V$	30pF	500 $\Omega$	500 $\Omega$
$3.3V \pm 0.3V$	30pF	500 $\Omega$	500 $\Omega$



**Note:**

9. Input  $t_R=t_F=2.0ns$ , 10% to 90%


Figure 3. Waveform for Inverting and Non-Inverting Functions



**Note:**

10. Input  $t_R=t_F=2.0ns$ , 10% to 90%

Figure 4. 3-State Output High Enable and Disable for Low Voltage Logic



**Note:**

11. Input  $t_R=t_F=2.0ns$ , 10% to 90%

Figure 5. 3-State Output High Enable and Disable for Low Voltage Logic

Symbol	$V_{CC}$				
	$3.3V \pm 0.3V$	$2.5V \pm 0.2V$	$1.8V \pm 0.15V$	$1.5V \pm 0.1V$	$1.2V \pm 0.1V$
$V_{MI}$	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$
$V_{MO}$	$V_{CC0}/2$	$V_{CC0}/2$	$V_{CC0}/2$	$V_{CC0}/2$	$V_{CC0}/2$
$V_X$	$V_{OH} - 0.3V$	$V_{OH} - 0.15V$	$V_{OH} - 0.15V$	$V_{OH} - 0.1V$	$V_{OH} - 0.1V$
$V_Y$	$V_{OL} + 0.3V$	$V_{OL} + 0.15V$	$V_{OL} + 0.15V$	$V_{OL} + 0.1V$	$V_{OL} + 0.1V$

**Note:**

12. For  $V_{MI}$   $V_{CC0}=V_{CCA}$  for control pins  $T/\bar{R}$  and  $\bar{O}E$  or  $V_{CC}/2$ .

## Functional Description

### Power-Up/Power-Down Sequencing

FXL translators offer an advantage in that either  $V_{CC}$  may be powered up first. This benefit derives from the chip design. When either  $V_{CC}$  is at 0V, outputs are in a High-impedance state. The control inputs ( $\overline{T/R}$  and  $\overline{OE}$ ) are designed to track the  $V_{CCA}$  supply. A pull-up resistor tying  $\overline{OE}$  to  $V_{CCA}$  should be used to ensure that bus contention, excessive currents, or oscillations do not occur during power-up/power-down. The size of the pull-up resistor is based upon the current-sinking capability of the OE driver.


The recommended power-up sequence is:

1. Apply power to either  $V_{CC}$ .
2. Apply power to the  $\overline{T/R}$  input (logic HIGH for A-to-B operation; logic LOW for B-to-A operation) and to the respective data inputs (A port or B port). This may occur at the same time as step 1.
3. Apply power to the other  $V_{CC}$ .
4. Drive the  $\overline{OE}$  input LOW to enable the device.

The recommended power-down sequence is:

1. Drive  $\overline{OE}$  input HIGH to disable the device.
2. Remove power from either  $V_{CC}$ .
3. Remove power from the other  $V_{CC}$ .

## Physical Dimensions



### NOTES:

- A. CONFORMS TO JEDEC REGISTRATION MO-220, VARIATION WFS-2 FOR DIMENSIONS ONLY. PIN NUMBERING DOES NOT COMPLY.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994

MLP24Brev4

**Figure 6. 24-Pin Molded Leadless Package (MLP), JEDEC MO-220, 3.5 x 4.5mm**

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.








Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:  
<http://www.fairchildsemi.com/packaging/>.

For current tape and reel specifications, visit Fairchild Semiconductor's online packaging area:  
[http://www.fairchildsemi.com/packaging/MLP24B\\_TNR.pdf](http://www.fairchildsemi.com/packaging/MLP24B_TNR.pdf).



**TRADEMARKS**

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

- |   |   |   |   |
|---|---|---|---|
| Auto-SPM™   | F-PFST™   | PowerTrench®  | The Power Franchise®  |
| Build it Now!™  | FRFET®  | PowerXS™  |  the power franchise |
| CorePLUSTM  | Global Power Resource <sup>SM</sup>   | Programmable Active Droop™  | TinyBoost™  |
| CorePOWER™  | Green FPST™   | QFET®   | TinyBuck™   |
| CROSSVOLT™  | Green FPST™ e-Series™   | QS™   | TinyLogic®  |
| CTL™  | Gmax™   | Quiet Series™   | TINYOPTO™   |
| Current Transfer Logic™   | GTO™  | RapidConfigure™   | TinyPower™  |
| EcoSPARK®   | IntelliMAX™   |  TM              | TinyPWM™  |
| EfficientMax™   | ISOPLANAR™  | Saving our world, 1mW/W/kW at a time™   | TinyWire™   |
| EZSWITCH™   | MegaBuck™   | SmartMax™   | TriFault Detect™  |
|  ™ | MICROCOUPLER™   | SMART START™  | TRUECURRENT™  |
|  ™ | MicroFET™   | SPM®  | µSerDes™  |
| Fairchild®  | MicroPak™   | STEALTH™  |  SerDes®             |
| Fairchild Semiconductor®  | MillerDrive™  | SuperFET™   | UHC®  |
| FACT Quiet Series™  | MotionMax™  | SuperSOT™.3   | Ultra FRFET™  |
| FACT®   | Motion-SPM™   | SuperSOT™.6   | UniFET™   |
| FAST®   | OPTOLOGIC®  | SuperSOT™.8   | VXC™  |
| FastvCore™  | OPTOPLANAR®   | SupreMOS™   | VisualMax™  |
| FETBench™   |  ™ | SyncFET™  | XST™  |
| FlashWriter®  | PDP SPM™  | Sync-Lock™  |   |
| FPST™   | Power-SPM™  |  SYSTEM GENERAL® |   |

\* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

**DISCLAIMER**

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

**LIFE SUPPORT POLICY**

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**ANTI-COUNTERFEITING POLICY**

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.fairchildsemi.com](http://www.fairchildsemi.com), under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

**PRODUCT STATUS DEFINITIONS**

**Definition of Terms**

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev. 140

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA  
**Phone:** 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada  
**Europe, Middle East and Africa Technical Support:**  
Phone: 421 33 790 2910  
**Japan Customer Focus Center**  
Phone: 81-3-5817-1050

**ON Semiconductor Website:** [www.onsemi.com](http://www.onsemi.com)  
**Order Literature:** <http://www.onsemi.com/orderlit>  
For additional information, please contact your local  
Sales Representative