

Circular cutter, Lilliput type

for diameter range from 18-80 mm

Application:


For drilling holes in the diameter range from 18 to 80 mm up to a max. material thickness of 30 mm in steel, non-ferrous metals, seals, rubber, leather and similar materials.

Execution:

- steel circular cutter with cutter holder and cutter, HSS, type 122

Advantage:

- universal use for a multitude of materials
- possible to create cost-effective holes in a large diameter range
- excellent cutting properties and high degree of cutting precision



Art. no.	11350 011
Brand	GFS
Manufacturer Part Number	21 010 000
Type	Lilliput type with cutter, type 122 HSSE
Suitable for min. diameter	18 mm
Shank diameter	10 mm
Gross Weight	0.342 kg
Product Group	119