

## MWLN clamp holder, negative, right

For copy, longitudinal and face turning with WN indexable insert

**ATORN**<sup>®</sup>

### Application

For copy, longitudinal and face turning with WN indexable insert, 80°.

### Version

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type W, working angle 93°, tip angle 80°, clearance angle 0°

### Advantage

- Triple-edge geometry lowers cost per cut
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations
- Adjustable clamp minimises vibrations and ensures good force transfer



<b>Art. No.</b>	<b>17860 050</b>
<b>ISO name</b>	MWLN R/L 2525 M08
<b>Shaft height</b>	25 mm
<b>Shank width</b>	25 mm
<b>Length</b>	150 mm
<b>Programming size</b>	32 mm
<b>Length of head</b>	34 mm
<b>Suitable for indexable inserts</b>	WN.. 0804..
<b>Tool design</b>	Right
<b>DIN</b>	4983

### EAN-Code

4050293 127126