

Vornscheider Professional ESD



breiter Kopf mit kleiner Wate

Z 47 2 04

Best.-Nr.	mm	II	SB	Ømm	SB	Icon
26840	115	4 ½	2	1.4		5
27453	115	4 ½	2	1.4	x	5

DIN ISO 9654. IEC 61340-5-1.

Rundzange Professional ESD



runde, kurze Backen

Z 37 0 04

Best.-Nr.	mm	II	SB	Icon
26804	120	4 ¾		5
27440	120	4 ¾	x	5

DIN ISO 9655. IEC 61340-5-1.

Flachrundzange Professional ESD



gerade Form

Z 36 0 04

Best.-Nr.	mm	II	A	B	D	F	Icon
26799	120	4 ¾	9,5	23	6,5	1,4	5
27329	120	4 ¾	9,5	23	6,5	1,4	5
27905	145	5 ¾	12,0	40	7,5	2,0	5

DIN ISO 9655. IEC 61340-5-1.

Flachzange Professional ESD



flache, kurze Backen

Z 38 0 04

Best.-Nr.	mm	II	SB	Icon
26806	120	4 ¾		5
27441	120	4 ¾	x	5

DIN ISO 9655. IEC 61340-5-1.

Flachrundzange Professional ESD



gebogene Form, ca. 45°

Z 36 1 04

Best.-Nr.	mm	II	SB	Icon
26802	120	4 ¾		5
27439	120	4 ¾	x	5

DIN ISO 9655. IEC 61340-5-1.