

THP0301 Series Passive 10x Voltage Probe

THP0301-Y, THP0301-B, THP0301-M, THP0301-G



The THP0301 probes are 300 MHz, 10X passive voltage probes with 10 M Ω input resistance. These probes are for use with the THS3000 Series oscilloscopes and are color coded to match the oscilloscope's channel input connectors, front-panel channel selector buttons, and the displayed waveforms.

Key features

- 300 MHz bandwidth for the THS3000 series handheld oscilloscopes
- 10X attenuation
- 1.2 m length

Applications

- Low-frequency computer and telecom measurements
- Power supplies
- Low-frequency amplifiers
- Inverter design
- Power conversion

Safely measure from mV to kV

The THP0301 probes have a CAT III safety rating which matches the safety rating on the THS3000 Series oscilloscopes enabling you to safely measure voltage ranges from mV to kV. You'll be able to measure anything from micro-electronics to heavy-duty medium-voltage electrical applications, making it possible to obtain accurate measurements in mixed-signal environments with separate ground references.

For a complete list of compatible oscilloscopes, refer to the Tektronix Oscilloscope Probe & Accessory Selector Tool at <http://www.tek.com/probes>.

Specifications

All specifications apply to all models unless noted otherwise.

	Description
Bandwidth	DC to 300 MHz
Probe length	1.2 m
Compensation range	10 pF to 22 pF
Input capacitance	11 pF
Input resistance	10 MΩ
Maximum input voltage	300 v CAT III

Ordering information

Models

THP0301-Y	(Yellow) DC to 300 MHz, 10X high-voltage probe ¹
THP0301-B	(Blue) DC to 300 MHz, 10X high-voltage probe ¹
THP0301-M	(Magenta) DC to 300 MHz, 10X high-voltage probe ¹
THP0301-G	(Green) DC to 300 MHz, 10X high-voltage probe ¹

Optional accessories

020-3085-xx	Probe accessory replacement kit
-------------	---------------------------------



¹ One of each probe is included as a standard accessory with the THS3000 series oscilloscopes.

ASEAN / Australasia (65) 6356 3900
Belgium 00800 2255 4835*
Central East Europe and the Baltics +41 52 675 3777
Finland +41 52 675 3777
Hong Kong 400 820 5835
Japan 81 (3) 6714 3010
Middle East, Asia, and North Africa +41 52 675 3777
People's Republic of China 400 820 5835
Republic of Korea 001 800 8255 2835
Spain 00800 2255 4835*
Taiwan 886 (2) 2722 9622

Austria 00800 2255 4835*
Brazil +55 (11) 3759 7627
Central Europe & Greece +41 52 675 3777
France 00800 2255 4835*
India 000 800 650 1835
Luxembourg +41 52 675 3777
The Netherlands 00800 2255 4835*
Poland +41 52 675 3777
Russia & CIS +7 (495) 6647564
Sweden 00800 2255 4835*
United Kingdom & Ireland 00800 2255 4835*

Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777
Canada 1 800 833 9200
Denmark +45 80 88 1401
Germany 00800 2255 4835*
Italy 00800 2255 4835*
Mexico, Central/South America & Caribbean 52 (55) 56 04 50 90
Norway 800 16098
Portugal 80 08 12370
South Africa +41 52 675 3777
Switzerland 00800 2255 4835*
USA 1 800 833 9200

* European toll-free number. If not accessible, call: +41 52 675 3777

Updated 10 April 2013

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tektronix.com.

Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

19 Jun 2013



3GW-27122-2

