

Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

SECTION 1: Identification of the substance/mixture and of the company/undertaking

· 1.1 Product identifier

· Trade name: Chain Lubricant Spray E-COLL

· Article number: 4317784305587

· 1.2 Relevant identified uses of the substance or mixture and uses advised against

· Sector of Use

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

- · Application of the substance / the mixture Lubricant
- · 1.3 Details of the supplier of the safety data sheet
- · Manufacturer/Supplier:

E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH EDE Platz 1 D-42389 Wuppertal Germany

Tel. +49 202 6096-0 e-mail: sdb@ede.de

- · Further information obtainable from: Product safety department
- 1.4 Emergency telephone number: Giftinformationszentrum Mainz Tel.: +49 (6131) 19240

SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- · Classification according to Regulation (EC) No 1272/2008

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

Skin Irrit. 2 H315 Causes skin irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

Aquatic Chronic 3 H412 Harmful to aquatic life with long lasting effects.

· 2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms





GHS02 GHS07

· Signal word Danger

· Hazard-determining components of labelling:

Naphtha (petroleum), hydrotreated light (Benzene < 0.1%)



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 1)

Naphtha (petroleum), hydrotreated light

· Hazard statements

H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

H315 Causes skin irritation.

H336 May cause drowsiness or dizziness.

H412 Harmful to aquatic life with long lasting effects.

· Precautionary statements

P101	If medical advice is needed, have product container or label at hand
FIUI	II Medical advice is needed. Have product container of laber at hand

P102 Keep out of reach of children.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No

smokina.

P211 Do not spray on an open flame or other ignition source.

P251 Do not pierce or burn, even after use.

P261 Avoid breathing spray.

P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves.

P302+P352 IF ON SKIN: Wash with plenty of water.

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P312 Call a POISON CENTER/doctor if you feel unwell. P332+P313 If skin irritation occurs: Get medical advice/attention.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

P501 Dispose of contents/container in accordance with local/regional/national/international

regulations.

· 2.3 Other hazards

· Results of PBT and vPvB assessment

PBT: Not applicable.vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Chemical characterisation: Mixtures

· **Description:** Mixture of substances listed below with nonhazardous additions.

· Dangerous components:				
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27-xxxx	isobutane Flam. Gas 1, H220 Press. Gas (Comp.), H280	50-100%		
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21-xxxx	propane Flam. Gas 1, H220 Press. Gas (Comp.), H280	5-<10%		
	(Con-	td on na		

(Contd. on page 3)



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

		ontd. of page 2)		
EC number: 926-608-8 Reg.nr.: 01-2119786291-36-xxx	Naphtha (petroleum), hydrotreated light (Benzene < 0.1%) Flam. Liq. 2, H225 Asp. Tox. 1, H304 Aquatic Chronic 2, H411 STOT SE 3, H336	3-<5%		
EC number: 927-510-4 Reg.nr.: 01-2119475515-33-XXXX	Naphtha (petroleum), hydrotreated light Flam. Liq. 2, H225 Asp. Tox. 1, H304 Aquatic Chronic 2, H411 Skin Irrit. 2, H315; STOT SE 3, H336	3-<5%		
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32-xxxx	butane, pure The Flam. Gas 1, H220 Press. Gas (Comp.), H280	1-<3%		
CAS: 4259-15-8	zinc bis[O,O-bis(2-ethylhexyl)]bis(dithiophosphate) Eye Dam. 1, H318 Aquatic Chronic 2, H411	0.1-<1%		
· Regulation (EC) No 648/2004 on detergents / Labelling for contents				
aliphatic hydrocarbons				

· Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· 4.1 Description of first aid measures

· General information:

Personal protection for the First Aider. Immediately remove any clothing soiled by the product.

· After inhalation:

Supply fresh air.

Seek medical treatment in case of complaints.

· After skin contact:

Immediately wash with water and soap and rinse thoroughly.

If skin irritation continues, consult a doctor.

· After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

- · After swallowing: Drink plenty of water and provide fresh air. Call for a doctor immediately.
- 4.2 Most important symptoms and effects, both acute and delayed No further relevant information available.
- 4.3 Indication of any immediate medical attention and special treatment needed No further relevant information available.



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 3)

SECTION 5: Firefighting measures

- · 5.1 Extinguishing media
- · Suitable extinguishing agents: CO2, sand, extinguishing powder. Do not use water.
- · For safety reasons unsuitable extinguishing agents: Water
- 5.2 Special hazards arising from the substance or mixture Can form explosive gas-air mixtures.
- · 5.3 Advice for firefighters
- · Protective equipment: Do not inhale explosion gases or combustion gases.
- Additional information

Cool endangered receptacles with water spray.

Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures

· 6.1 Personal precautions, protective equipment and emergency procedures

Wear protective equipment. Keep unprotected persons away. Ensure adequate ventilation

· 6.2 Environmental precautions:

Inform respective authorities in case of seepage into water course or sewage system.

Do not allow to enter sewers/ surface or ground water.

· 6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Do not flush with water or aqueous cleansing agents

· 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

- 7.1 Precautions for safe handling Use only in well ventilated areas.
- · Information about fire and explosion protection:



Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

Do not spray onto a naked flame or any incandescent material.

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.

(Contd. on page 5)



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 4)

- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage:
- · Requirements to be met by storerooms and receptacles:

Store in a cool location.

Observe official regulations on storing packagings with pressurised containers.

- · Information about storage in one common storage facility: Store away from oxidising agents.
- · Further information about storage conditions:

Keep container tightly sealed.

Store in dry conditions.

Protect from heat and direct sunlight.

· 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

- Additional information about design of technical facilities: No further data; see item 7.
- · 8.1 Control parameters
- · Ingredients with limit values that require monitoring at the workplace:

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

- · Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls
- · Personal protective equipment:
- · General protective and hygienic measures:

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

· Respiratory protection:

Not necessary if room is well-ventilated.

Use suitable respiratory protective device in case of insufficient ventilation.

Filter A/P2

· Protection of hands:



· Material of gloves

Nitrile rubber, NBR

Recommended thickness of the material: ≥ 0.4 mm



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 5)

· Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye protection:



Tightly sealed goggles

· Body protection: Protective work clothing

SECTION 9: Physical and chemical properties

- · 9.1 Information on basic physical and chemical properties
- · General Information

· Appearance:

Form: Aerosol
Colour: Clear

Odour: CharacteristicOdour threshold: Not determined.

· **pH-value:** Not determined.

· Change in condition

Melting point/freezing point: Undetermined.

Initial boiling point and boiling range: Not applicable, as aerosol.

· Flash point: Not applicable, as aerosol.

· Flammability (solid, gas): Not applicable.

· Ignition temperature: 235 °C

• **Decomposition temperature:** Not determined.

· Auto-ignition temperature: Product is not selfigniting.

• Explosive properties: Not determined.

· Explosion limits:

Lower: 3.0 Vol %
Upper: 18.6 Vol %
• Oxidising properties Not determined.

· Vapour pressure at 20 °C: 6000 hPa

· Density at 20 °C: 0.77 g/cm³

(Contd. on page 7)



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 6)

· Relative density Not determined.

Vapour densityEvaporation rateNot determined.Not applicable.

· Solubility in / Miscibility with

water: Not miscible or difficult to mix.

· Partition coefficient: n-octanol/water: Not determined.

· Viscosity:

Dynamic: Not determined. **Kinematic:** Not determined.

 Organic solvents:
 57.0 %

 VOC (EC) %
 57.00 %

 VOC (EC) g/l
 438.9 g/l

 VOCV (CH)
 57.00 %

• 9.2 Other information No further relevant information available.

SECTION 10: Stability and reactivity

- 10.1 Reactivity No further relevant information available.
- · 10.2 Chemical stability
- \cdot Thermal decomposition / conditions to be avoided:

No decomposition if used according to specifications.

- · 10.3 Possibility of hazardous reactions No dangerous reactions known.
- 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- · 10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

- · 11.1 Information on toxicological effects
- · Acute toxicity Based on available data, the classification criteria are not met.
- · LD/LC50 values relevant for classification:

CAS: 74-98-6 propane

Inhalative LC50/4h >20 mg/m³ (rat)

CAS: 106-97-8 butane, pure

Inhalative LC50/4h 658 ppm (rat)

(Contd. on page 8)



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 7)

- · Primary irritant effect:
- Skin corrosion/irritation
 Causes skin irritation.
- · Serious eye damage/irritation Based on available data, the classification criteria are not met.
- · Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- · CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- · Carcinogenicity Based on available data, the classification criteria are not met.
- · Reproductive toxicity Based on available data, the classification criteria are not met.
- STOT-single exposure
 May cause drowsiness or dizziness.
- · STOT-repeated exposure Based on available data, the classification criteria are not met.
- · Aspiration hazard Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- 12.2 Persistence and degradability No further relevant information available.
- 12.3 Bioaccumulative potential No further relevant information available.
- · 12.4 Mobility in soil No further relevant information available.
- · Ecotoxical effects:
- · Remark: Toxic for fish
- · Additional ecological information:
- · General notes:

Toxic for aquatic organisms Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water Do not allow product to reach ground water, water course or sewage system.

- · 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.
- · vPvB: Not applicable.



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 8)

• 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods:
- · European waste catalogue

16 05 04* gases in pressure containers (including halons) containing hazardous substances

SECTION 14: Transport information

· 14.1 UN-Number

· ADR, IMDG, IATA UN1950

· 14.2 UN proper shipping name

· **ADR** UN1950 AEROSOLS, ENVIRONMENTALLY

HAZARDOUS

· IMDG AEROSOLS, MARINE POLLUTANT

· IATA AEROSOLS, flammable

· 14.3 Transport hazard class(es)

· ADR



· Class 2 5F Gases.

· Label 2.1

· IMDG, IATA



• Class 2.1 • Label 2.1

· 14.4 Packing group

· ADR, IMDG, IATA Void

· 14.5 Environmental hazards:

· Marine pollutant: Yes

• 14.6 Special precautions for user Warning: Gases.

Hazard identification number (Kemler code):

· **EMS Number**: F-D,S-U

· 14.7 Transport in bulk according to Annex II of

Marpol and the IBC Code Not applicable.

(Contd. on page 10)



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 9)

· Transport/Additional information:

· ADR

Limited quantities (LQ)
 Transport category
 Tunnel restriction code

· UN "Model Regulation": UN 1950 AEROSOLS, 2.1, ENVIRONMENTALLY

HAZARDOUS

SECTION 15: Regulatory information

- · Directive 2012/18/EU
- Named dangerous substances ANNEX I Methanol
- · Seveso category

P3a FLAMMABLE AEROSOLS

E2 Hazardous to the Aquatic Environment

- · Qualifying quantity (tonnes) for the application of lower-tier requirements 150 t
- · Qualifying quantity (tonnes) for the application of upper-tier requirements 500 t
- · REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3
- · 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.
- · Exposure scenario(s)

Exposure scenario(s) of ingredients (if present) are available on request at: sdb@ede.de

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Relevant phrases

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H280 Contains gas under pressure; may explode if heated.

H304 May be fatal if swallowed and enters airways.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H336 May cause drowsiness or dizziness.

H411 Toxic to aquatic life with long lasting effects.

· Department issuing SDS: Product safety department

· Contact: sdb@ede.de

Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances



Printing date 25.09.2020 Version number 302 Revision: 25.09.2020

Trade name: Chain Lubricant Spray E-COLL

(Contd. of page 10)

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOCV: Lenkungsabgabe auf flüchtigen organischen Verbindungen, Schweiz (Swiss Ordinance on volatile organic compounds)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic vPvB: very Persistent and very Bioaccumulative Flam. Gas 1: Flammable gases - Category 1

Aerosol 1: Aerosols - Category 1

Press. Gas (Comp.): Gases under pressure - Compressed gas

Flam. Liq. 2: Flammable liquids - Category 2

Skin Irrit. 2: Skin corrosion/irritation - Category 2

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

STOT SE 3: Specific target organ toxicity (single exposure) - Category 3

Asp. Tox. 1: Aspiration hazard - Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard - Category 2 Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard - Category 3

· * Data compared to the previous version altered.