

Product type designation



Reader RF260R ASCII

SIMATIC RF200 READER RF260R; RS232 INTERFACE (ASCII); IP 67, -25 UP TO +70 DGR/C; 75 X 75 X 40 MM; WITH INTEGRATED ANTENNA.

Suitability for operation

ISO 15693 Transponder (MDS Dxxx), for connecting to PC- and control systems

Wireless frequencies

Operating frequency / Rated value

13.56 MHz

Electrical data

Range / maximum

135 mm; Range is dependent on transponder type: observe <http://support.automation.siemens.com/WW/view/en/67384964>

Protocol / with radio transmission

ISO 15693, ISO 18000-3

Transfer rate / with radio transmission / maximum

26.5 kbit/s

Product property / multitag-capable

No

Transfer rate / at the point-to-point connection / serial / maximum

115.2 kbit/s

Transmission time / for user data

- for write access / per byte / typical
- for read access / per byte / typical

1.2 ms

1.2 ms

Interfaces

Standard for interfaces / for communication

RS232

Type of electrical connection

M12, 8-pin

Mechanical data

Material

PA6.6

Color

anthracite

Tightening torque / of the screw for securing the equipment / maximum

1.5 N·m

Mounting distance / relating to metal surfaces / recommended / minimum	0 mm
Supply voltage, current consumption, power loss	
Supply voltage	
• for DC / Rated value	24 V
• for DC	20.4 ... 28.8 V
Consumed current / for DC / at 24 V	
• typical	0.05 A
Permitted ambient conditions	
Ambient temperature	
• during operation	-20 ... +70 °C
• during storage	-25 ... +80 °C
• during transport	-25 ... +80 °C
Protection class IP	IP67
Shock resistance	EN 60721-3-7, Class 7 M2
Shock acceleration	500 m/s ²
Resistance against vibration	200 m/s ²
Design, dimensions and weight	
Width	75 mm
Height	41 mm
Depth	75 mm
Net weight	0.2 kg
Mounting type	2 x M5 screws
Cable length	
• with RS 232 interface / maximum	30 m
Product properties, functions, components / general	
Display version	3-color LED
Product property / silicon-free	Yes
Standards, specifications, approvals	
Certificate of suitability	Wireless according to R&TTE guidelines EN300 330 and EN 301489, FCC, UL/CSA
MTBF	430 y
Further Information / Internet Links	
Internet-Link	
• to website: Selector SIMATIC NET SELECTION TOOL	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/automation/net/catalog
• to website: Image database	http://automation.siemens.com/bilddb

- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

10.03.2015