

Description

Very cost effective design to meet international requirements. No exposed metal parts which are, or could become, current-carrying except for terminals. R-type TO CBE to EN 60934.

- Manual reset, cycling trip free mechanism
- Extremely small and lightweight
- UL, CSA, VDE and EN 60934 (IEC 60934) approved

Typical applications

Battery chargers, consumer products, power supplies, motors.

Ordering information

Type No.	
1658	single pole thermal circuit breaker
Threadneck design	
G21	manual reset type, 3/8"-27 threadneck
G41	manual reset type, 7/16"-28 threadneck
A21	auto reset type, 3/8"-27 threadneck
A41	auto reset type, 7/16"-28 threadneck
A00	auto reset type, without threadneck
F01	snap in
Hardware	
00	no hardware
01	one PAL nut, bulk
02	one PAL nut, one knurled nut, bulk
03	one PAL nut mounted
04	one PAL nut, one knurled nut, mounted
05	one PAL nut mounted, one knurled nut, bulk
06	one knurled nut, bulk
07	one hex nut, bulk
08	two hex nuts, bulk
Terminals	
P10	blade terminals A6.3-0.8 (QC .250)
P13	blade terminals A6.3-0.8 (QC .250), 90°
S80	straight screw terminals*
S83	90° bent screw terminals*
Current ratings	
5 ...30 A	
1658 - G21 - 02 - P10 - 5 A Ordering example	

* Screws and lock washers bulk shipped



1658-...

Technical data

For further details please see chapter: Technical Information

Voltage rating	AC 240 V; DC 28 V		
Current ratings	5...30 A		
Typical life	AC + DC	5...16 A	1,000 operations at 2 x I _N , inductive
		17...25 A	1,000 operations at 2 x I _N , resistive
Ambient temperature	-20...+60 °C (-4...+140 °F), ≤ 7 A max. +40 °C (+104 °F)		
Insulation co-ordination (IEC 60664 and 60664 A)	rated impulse withstand voltage	2.5 kV	pollution degree 2
	reinforced insulation in operating area		
Dielectric strength (IEC 60664 and 60664A) operating area	test voltage	AC 3,000 V	
Insulation resistance	> 100 MΩ (DC 500 V)		
Interrupting capacity I _{cn}	5...7 A	180 A	
	8...30 A	200 A	
Interrupting capacity (UL 1077/EN 60934 PC1)	I _N	U _N	
	5...16 A	AC 240 V	2,000 A
	18...30 A	AC 120 V	2,000 A
	5...30 A	DC 28 V	2,000 A
Degree of protection (IEC 60529/DIN 40050)	operating area IP40 terminal area IP00		
Vibration	8 g (57-500 Hz) ±0.61 mm (10-57 Hz), to IEC 60068-2-6, test Fc, 10 frequency cycles/axis		
Shock	30 g (11 ms) to IEC 60068-2-27, test Ea		
Corrosion	96 hours at 5 % salt mist, to IEC 60068-2-11, test Ka		
Humidity	240 hours at 95 % RH to IEC 60068-2-78, test Cab		
Mass	approx. 16 g		


Standard current ratings and typical voltage drop values

Current rating (A)	Voltage drop (mV)	Current rating (A)	Voltage drop (mV)
5	≤ 150	12	≤ 140
6	≤ 150	15	≤ 240
7	≤ 150	16	≤ 240
8	≤ 150	20	≤ 240
9	≤ 150	25	≤ 240
10	≤ 140	30	≤ 240

Approvals

Authority	Voltage rating	Current ratings
VDE (EN 60934)	AC 240 V; DC 28 V	5...25 A
UL	AC 240 V	5...16 A 1658-G...
	AC 120 V	20...30 A 1658-G...
	AC 120 V	5...30 A 1658-A...
	DC 28 V	5...30 A 1658-G...

Dimensions





A00





A21

tightening torque max. 0.8 Nm
3/8-27UNS-2A





G21

tightening torque max. 0.8 Nm
3/8-27UNS-2A




A41

10
.394





G41

10
.394



7/16-28UNS-2A
double "D"
tightening torque max. 0.8 Nm

F01




Caution:
Please keep a tight grip on the unit
while removing the female connectors.

See ordering information for mounting hardware.


Terminal design

P10




blade terminals DIN 46244-A6.3-0.8
(QC .250)

S83




terminal screw
6-32 UNC
lock washer

P13




blade terminals DIN 46244-A6.3-0.8 (QC .250)
angled 90°

P10-S83



terminal screw
6-32 UNC
lock washer


S80



terminal screw
6-32 UNC
lock washer


blade terminals
DIN 46244-A6.3-0.8 (QC .250)

Installation drawing




This is a metric design and millimeter dimensions take precedence (mm/inch)

Internal connection diagram



Typical time/current characteristics




The time/current characteristic curve depends on the ambient temperature prevailing. In order to eliminate nuisance tripping, please multiply the circuit breaker current ratings by the derating factor shown below. See also section 9 – Technical information.


Ambient temperature	-4	+14	+32	+73.4	+104	+122	+140	
°F	-4	+14	+32	+73.4	+104	+122	+140	
°C	-20	-10	0	+23	+40	+50	+60	
Derating factor	$I_N > 7A$	0.83	0.85	0.9	1	1.1	1.18	1.25
	$I_N \leq 7A$	0.74	0.76	0.82	1	1.23	-	-

Accessories


Mounting nut 3/8", 27-thread
Y306 671 01




Mounting nut 7/16", 28-thread
Y303 200 01




Knurled nut 3/8", 27-thread plastic (standard)
Y307 117 02




Knurled nut 7/16", 28-thread nickel-plated brass
Y302 294 03




Knurled nut 3/8", 27-thread nickel-plated brass
Y300 190 03




Hex nut 3/8", 27-thread nickel-plated brass
Y300 192 01




Hex nut 7/16", 28-thread nickel-plated brass
Y302 295 01



Press to Reset Plate for 3/8" thread, aluminium
Y 301 059 02




Press to Reset Plate for 7/16" thread, aluminium
Y 302 732 01




Accessories

Reset button seal for 3/8", 27-thread,
short
X201 285 01

long
X200 799 01




3/8-27 UNS-2B




3/8-27 UNS-2B

Reset button seal for 7/16", 28-thread,
short
X222 119 01

long
X222 119 02



7/16-28 UNS-2B



7/16-28 UNS-2B

1

This is a metric design and millimeter dimensions take precedence ($\frac{\text{mm}}{\text{inch}}$)

All dimensions without tolerances are for reference only. In the interest of improved design, performance and cost effectiveness the right to make changes in these specifications without notice is reserved. Product markings may not be exactly as the ordering codes. Errors and omissions excepted.