

Printing date 12.04.2019 Version number 9 Revision: 12.04.2019

#### SECTION 1: Identification of the substance/mixture and of the company/undertaking

- · 1.1 Product identifier
- · Trade name: PICA TUBE 575
- · 1.2 Relevant identified uses of the substance or mixture and uses advised against

No further relevant information available.

- · Application of the substance / the mixture Industrial marker
- · 1.3 Details of the supplier of the safety data sheet
- · Manufacturer/Supplier:

PICA-MARKER GMBH

Pica-Str. 5

91356 Kirchehrenbach

**GERMANY** 

info@pica-marker.com

- · Further information obtainable from: Département sécurité du produit
- · 1.4 Emergency telephone number:
- BG: National Clinical Toxicology Centre, Tel.: +359 2 9154 409
- DK: Giftlingen Bispebjerg Hospital, Tel.: +45 82 12 12 12
- EE: Mürgistusteabekeskus, Tel.: +372 626 93 90
- GR: Poisons Information Centre, Tel.: +30 10 779 37777
- HR: Poisons Control Centre, Tel.: +385 1 234 8342
- HU: Orszagos Kemiai Biztonsagi Intézet, Tel.: +36 80 20 11 99
- IE: National Poisons Information Centre, Tel.: +353 1 809 2166
- LT: Apsinuodijimu kontrolès ir informacijos biuras, Tel.: +370 5 236 20 52
- LV: Valsts Toksikologijas centra, Tel.: +371 67 04 24 73
- SI: Poison Centre, Tel.: +386 41 650 500

### SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- · Classification according to Regulation (EC) No 1272/2008



GHS02 flame

Flam. Liq. 3 H226 Flammable liquid and vapour.



STOT SE 3 H336 May cause drowsiness or dizziness.

- · 2.2 Label elements
- · Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms





GHS02

GHS07

- · Signal word Warning
- · Hazard-determining components of labelling:
- n-butyl acetate
- · Hazard statements

H226 Flammable liquid and vapour.

H336 May cause drowsiness or dizziness.

(Contd. on page 2)



Printing date 12.04.2019 Version number 9 Revision: 12.04.2019

Trade name: PICA TUBE 575

(Contd. of page 1)

· Precautionary statements

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No

smoking.

P241 Use explosion-proof electrical/ventilating/lighting equipment.

P261 Avoid breathing dust/fume/gas/mist/vapours/spray.

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with

water/shower.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local/regional/national/international

regulations.

· Labelling of packages where the contents do not exceed 125 ml

· Hazard pictograms





GHS02 GHS07

- · Signal word Warning
- · Hazard-determining components of labelling:

n-butyl acetate

- · Hazard statements Void
- · 2.3 Other hazards
- · Results of PBT and vPvB assessment
- · **PBT:** Not applicable.
- · vPvB: Not applicable.

### SECTION 3: Composition/information on ingredients

- · 3.2 Chemical characterisation: Mixtures
- · Description: Mixture of substances listed below with nonhazardous additions.

· Dangerous	components:
-------------	-------------

• Additional information: For the wording of the listed hazard phrases refer to section 16.

### **SECTION 4: First aid measures**

- · 4.1 Description of first aid measures
- · General information: Immediately remove any clothing soiled by the product.
- · After inhalation: Supply fresh air; consult doctor in case of complaints.
- · After skin contact: Immediately rinse with water.
- · After eye contact: Rinse opened eye for several minutes under running water.
- · After swallowing: If symptoms persist consult doctor.
- · 4.2 Most important symptoms and effects, both acute and delayed No further relevant information available.
- · 4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

#### **SECTION 5: Firefighting measures**

- · 5.1 Extinguishing media
- · Suitable extinguishing agents:

CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

- · For safety reasons unsuitable extinguishing agents: Water with full jet
- 5.2 Special hazards arising from the substance or mixture No further relevant information available.

(Contd. on page 3)



Printing date 12.04.2019 Version number 9 Revision: 12.04.2019

Trade name: PICA TUBE 575

(Contd. of page 2)

· 5.3 Advice for firefighters

· Protective equipment: No special measures required.

#### SECTION 6: Accidental release measures

· 6.1 Personal precautions, protective equipment and emergency procedures

Wear protective equipment. Keep unprotected persons away.

- 6.2 Environmental precautions: Do not allow to enter sewers/ surface or ground water.
- · 6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Dispose contaminated material as waste according to item 13.

Ensure adequate ventilation.

· 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

### SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

Ensure good ventilation/exhaustion at the workplace.

Prevent formation of aerosols.

· Information about fire - and explosion protection:

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage:
- Requirements to be met by storerooms and receptacles: No special requirements.
- · Information about storage in one common storage facility: Not required.
- · Further information about storage conditions: Keep container tightly sealed.
- $\cdot \textit{Storage class:} \ \textit{Store in accordance with local/regional/national/international regulations}.$
- · 7.3 Specific end use(s) No further relevant information available.

#### SECTION 8: Exposure controls/personal protection

- · Additional information about design of technical facilities: No further data; see item 7.
- · 8.1 Control parameters
- Ingredients with limit values that require monitoring at the workplace:

#### 123-86-4 n-butyl acetate

WEL Short-term value: 966 mg/m³, 200 ppm Long-term value: 724 mg/m³, 150 ppm

- · Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls
- · Personal protective equipment:
- · General protective and hygienic measures:

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

- Respiratory protection: Not necessary if room is well-ventilated.
- · Protection of hands:



(Contd. on page 4)



Printing date 12.04.2019 Version number 9 Revision: 12.04.2019

Trade name: PICA TUBE 575

(Contd. of page 3)

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

- · Material of gloves Nitrile rubber, NBR
- Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye protection:



Tightly sealed goggles

SECTION 9: Physical and chemical properties	SECTION 9:	: Physical	and chemical	properties
---	------------	------------	--------------	------------

7.1 Injuintation on busic physical and chemical properties	· 9.1 Information on	basic physical	and chemical	properties
--	----------------------	----------------	--------------	------------

· General Information

· Appearance:

Form: Fluid

Colour: According to product specification

Odour: CharacteristicOdour threshold: Not determined.

· pH-value: Not determined.

· Change in condition

**Melting point/freezing point:** Undetermined. **Initial boiling point and boiling range:** 124-128 °C

· Flash point: 27 °C

· Flammability (solid, gas): Not applicable.

• Ignition temperature: 370 °C

· Decomposition temperature: Not determined.

· Auto-ignition temperature: Product is not selfigniting.

• Explosive properties: Product is not explosive. However, formation of explosive air/

vapour mixtures are possible.

· Explosion limits:

 Lower:
 1.2 Vol %

 Upper:
 7.5 Vol %

· Vapour pressure at 20 °C: 10.7 hPa

Density at 20 °C: ~1.91~1.92 g/cm³
 Relative density Not determined.
 Vapour density Not determined.
 Evaporation rate Not determined.

· Solubility in / Miscibility with

water: Not miscible or difficult to mix.

· Partition coefficient: n-octanol/water: Not determined.

· Viscosity:

**Dynamic:** Not determined. **Kinematic at 20 °C:** 300 s (ISO 6 mm)

· Solvent content:

 Organic solvents:
 37.3 %

 VOC (EC)
 37.26 %

(Contd. on page 5)



Printing date 12.04.2019 Version number 9 Revision: 12.04.2019

Trade name: PICA TUBE 575

(Contd. of page 4)

Solids content: 40.9 %

• 9.2 Other information No further relevant information available.

### SECTION 10: Stability and reactivity

- · 10.1 Reactivity No further relevant information available.
- · 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.
- · 10.3 Possibility of hazardous reactions No dangerous reactions known.
- · 10.4 Conditions to avoid No further relevant information available.
- · 10.5 Incompatible materials: No further relevant information available.
- · 10.6 Hazardous decomposition products: No dangerous decomposition products known.

### SECTION 11: Toxicological information

- · 11.1 Information on toxicological effects
- · Acute toxicity Based on available data, the classification criteria are not met.
- · Primary irritant effect:
- Skin corrosion/irritation Based on available data, the classification criteria are not met.
- · Serious eye damage/irritation Based on available data, the classification criteria are not met.
- · Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- · CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- · Carcinogenicity Based on available data, the classification criteria are not met.
- · Reproductive toxicity Based on available data, the classification criteria are not met.
- · STOT-single exposure

May cause drowsiness or dizziness.

- · STOT-repeated exposure Based on available data, the classification criteria are not met.
- · Aspiration hazard Based on available data, the classification criteria are not met.

#### SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- · 12.2 Persistence and degradability No further relevant information available.
- · 12.3 Bioaccumulative potential No further relevant information available.
- · 12.4 Mobility in soil No further relevant information available.
- · Additional ecological information:
- · General notes:

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water

Do not allow product to reach ground water, water course or sewage system.

Danger to drinking water if even small quantities leak into the ground.

- · 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.
- · vPvB: Not applicable.
- · 12.6 Other adverse effects No further relevant information available.

#### SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods
- · Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

(Contd. on page 6)



Printing date 12.04.2019 Version number 9 Revision: 12.04.2019

Trade name: PICA TUBE 575

(Contd. of page 5)

· Uncleaned packaging:

· Recommendation: Disposal must be made according to official regulations.

SECTION 14: Transport informa	tion	
14.1 UN-Number		
ADR, ADN, IMDG	not regulated	
IATA	UN1263	
14.2 UN proper shipping name		
ADR, ADN, IMDG	not regulated	
IATA	PAINT	
14.3 Transport hazard class(es)		
ADR, ADN, IMDG		
Class	not regulated	
Class	2 Elammahla liawida	
Label	3 Flammable liquids. 3	
	<u> </u>	
14.4 Packing group		
ADR, IMDG IATA	not regulated III	
	III	
14.5 Environmental hazards:	M	
Marine pollutant:	No	
14.6 Special precautions for user	Not applicable.	
14.7 Transport in bulk according to Ann		
Marpol and the IBC Code	Not applicable.	

### **SECTION 15: Regulatory information**

- · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- · Directive 2012/18/EU
- · Named dangerous substances ANNEX I None of the ingredients is listed.
- · Seveso category P5c FLAMMABLE LIQUIDS
- Qualifying quantity (tonnes) for the application of lower-tier requirements 5,000 t
- Qualifying quantity (tonnes) for the application of upper-tier requirements 50,000 t
- REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3
- · 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H226 Flammable liquid and vapour.

(Contd. on page 7)



Printing date 12.04.2019 Version number 9 Revision: 12.04.2019

Trade name: PICA TUBE 575

(Contd. of page 6)

H336 May cause drowsiness or dizziness.

- · Department issuing SDS: Service protection de l'environnement
- · Contact: Responsable QHSE
- · Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU) PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Flam. Liq. 3: Flammable liquids – Category 3

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

\* \* Data compared to the previous version altered.

GB