


RoHS
Compliant



Coil Data

Nominal Voltage	: 12V DC
Coil Resistance	: 90Ω ±10% at 23°C
Nominal Current	: 133.3mA ±10% at 23°C
Operating Voltage	: 8.4V DC Max.
Release Voltage	: 1.2V DC Min.
Max. Coil Voltage	: 15.6V DC (130% of Nominal Voltage)
Nominal Operating Power	: 1600mW

Contact Data

Contact Form	: 1 Form A-SPST
Contact Material	: Ag Alloy
Contact Rating	: Resistive: 40A 14V DC
Max. Switching Voltage	: 75V DC
Max. Continuous Current	: 60A (23°C 10min)
Max. Inrush Current	: 100A
Contact Resistance (Initial)	: Max. 100mΩ at 6V DC 1A
Electrical Durability	: 100,000 cycles at room temperature (720 cycles/h) After test, the dielectric strength shall be not less than 75% of initial value
Mechanical Durability	: 10,000,000 operations at no load (18,000 ops / hour)


General Data

Insulation Resistance	: Min .100MΩ at 500V DC
Dielectric Strength	: Leakage current: 1mA
(1) Between Contacts	: 500V AC, 1min, 50 / 60Hz
(2) Between Coil and Contact	: 500V AC, 1min, 50 / 60Hz
Operate Time	: Max. 10ms.
Release Time	: Max. 10ms.
Operating Temperature	: -40°C to +85°C
Storage Conditions	
(1) Storage Temperature	: -40°C to +85°C
(2) Environments	: Store in locations where the product is not exposed to corrosive gas such as hydrogen sulfide gas or salty air. Store in locations where the product is not exposed to the direct ray of the sun and rain, snow.
Temperature Rise Coil	: 70k max. by resistance method when 40A current is applied to contact and 100% of rated voltage to coil at 85°C
Terminal Strength Tensile and pushing	: To be free from any abnormality in both the construction and characteristics after pushing and pulling the relay terminal 2mm from the body with 10kg for 10sec.
Cold and Heat Resistance	: Less than 100mΩ
Heat Shock	: Less than 100mΩ and insulation resistance shall be more than 10MΩ.
Damp Heat Cyclic Test	: Less than 100mΩ and insulation resistance shall be more than 10MΩ .

Voltage Monitoring Relay

multicomp PRO

Diagram



Part Number Table

Description	Part Number
Voltage Monitoring Relay, SPST, 12V DC, 40A	CMA31-DC12V-A

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO