

## PRODUCT DATASHEET

### VALUE PAR 16 80 36 ° 6.9 W/2700 K GU10

LED VALUE PAR16 | LED reflector lamps PAR16 with retrofit pin base



#### Areas of application

- Shops and exhibition rooms
- Domestic applications
- Commercial applications
- Accent lighting
- Outdoor use in suitable outdoor luminaires only

#### Product benefits

- Quick, simple and safe replacement without rewiring
- Design, dimensions, luminous flux comparable to an incandescent or halogen lamp
- Low maintenance costs thanks to long lifetime
- No UV and near-IR radiation in the light beam
- Instant 100 % light, no warm-up time

#### Product features

- LED alternative to high voltage halogen lamps
- Not dimmable
- Base: GU10
- Lamp made of glass
- Good quality of light; color rendering index  $R_a \geq 80$



## TECHNICAL DATA

### Electrical data

Nominal wattage	6.9 W
Construction wattage	6.90 W
Nominal voltage	220...240 V
Claimed equiv. conventional lamp power	80 W
Nominal current	54 mA
Type of current	AC
Inrush current	12 A
Operating frequency	50...60 Hz
Mains frequency	50...60 Hz
Max. lamp no. on circuit break. 10 A (B)	290
Max. lamp no. on circuit break. 16 A (B)	470
Power factor $\lambda$	> 0.50

### Photometrical data


Luminous intensity	1150 cd
Luminous flux	575 lm
Nominal useful luminous flux 90°	575 lm
Luminous efficacy	83 lm/W
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Color rendering index Ra	≥80
Light color	827
Standard deviation of color matching	≤6 sdcn
Rated peak intensity	1150 cd
Flickering metric (Pst LM)	1
Stroboscope effect metric (SVM)	0.9



### Light technical data

Beam angle	36 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

### Dimensions & Weight



Overall length	54.00 mm
Diameter	50.00 mm
Maximum diameter	50 mm
Product weight	42.00 g

### Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
Maximum temperature at tc test point	82 °C

### Lifespan

Lifespan	15000 h <sup>1)</sup>
Number of switching cycles	100000
Lumen maintenance at end of service lifetime	0.70

1) L70/B50

### Additional product data

Base (standard designation)	GU10
Mercury content	0.0 mg
Mercury-free	Yes

Product remark	All technical parameters apply to the entire lamp / Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value
----------------	--

### Capabilities

Dimmable	No
----------	----

### Certificates & Standards

Energy efficiency class	F <sup>1)</sup>
Energy consumption	7.00 kWh/1000h
Type of protection	IP20
Standards	CE / EAC
Photobiological safety group acc. to EN62778	RG1

<sup>1)</sup> Energy efficiency class (EEC) on a scale of A++ (highest efficiency) to E (lowest efficiency)

### Country-specific categorizations

Order reference	LVPAR168036 6,9
-----------------	-----------------

### Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	DLS
Mains or non-mains	MLS
Light source cap-type (or other electric interface)	GU10
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Standby power	0.00 W
Networked standby power for CLS	0.00 W
Claim of equivalent power	Yes
Length	54.00 mm
Height	50.00 mm
Width	50.00 mm
Chromaticity coordinate x	0.4578

Chromaticity coordinate y	0.411
R9 Colour rendering index	>0
Beam angle correspondence	NARROW_CONE_90
Survival factor	0.9
Displacement factor	>0.5
LED light source replaces a fluorescent light source	No
EPREL ID	686621
Model number	AC32044

## DOWNLOAD DATA

### Photometric and lighting design files



Spectral power distribution

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075198760	Folding box 1	52 mm x 52 mm x 60 mm	55.00 g	0.16 dm <sup>3</sup>
4058075198777	Shipping box 10	270 mm x 114 mm x 72 mm	623.00 g	2.22 dm <sup>3</sup>
4058075198784	Shipping box 80	446 mm x 275 mm x 173 mm	5546.00 g	21.22 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.