



# System 273 ESD-Safe

System 273 ESD-Safe Binocular Microscopes – designed for inspection and assembly applications in static-sensitive environments. The body and stand are powder-coated with a metal-laced paint that measures  $10^5 \Omega/\text{sq.}$  (static dissipative). These microscopes offer nearly 8 in. (203 mm) working distance (when used with an accessory 0.5X reducing lens) and 15% greater field of view than comparable scopes.



- Designed for use in static-sensitive environments
- $10^5 \Omega/\text{sq.}$  (static dissipative) powder coated body and stand
- Nearly 8 in. (203 mm) of working distance (when used with an accessory 0.5X reducing lens)
- Alters angles up to  $45^\circ$ , the head can be rotated  $360^\circ$  in its focus mount
- Dual boom ball-bearing stand with 10 in. x 10 in. base, 19.5 in. (495 mm) vertical boom and 26 in. (660 mm) horizontal boom extension



## RELATED PRODUCTS



[Lighting Options](#)



[System 250](#)



[System 273](#)



CODES

SYSTEM 273 ESD-SAFE, S-Z 23MM BINOCULAR MICROSCOPES

---

<b>Article Number</b>	<b>Weight</b>	<b>Mount</b>	<b>Lighting</b>
23712RB-ESD	61.7	Ball-Bearing Stand	FL Ring Light
23714RB-ESD	59.5	Ball-Bearing Stand -	
23726RB-ESD	61.7	Ball-Bearing Stand	LED-3000 Ring Light

ACCESSORIES

DESIGNATION

0.7X Lens, 23mm	23736
0.5X Lens, 23mm	23750