

Han Fast-Lock 10qmm ang.silverplate.+pin



-	-	
	Part number	09 08 000 7224
	Specification	Han Fast-Lock 10qmm ang.silverplate. +pin
	HARTING eCatalogue	https://b2b.harting.com/09080007224

Image is for illustration purposes only. Please refer to product description.

Identification

RoHS exemptions

Category	Contacts			
Series	Han-Fast [®] Lock			
Type of contact	PCB contact			
Description of the contact	With pin Angled			
Version				
Pack contents	Single contact			
Technical characteristics				
Conductor cross-section	10 mm ²			
Rated current	≤60 A			
Contact resistance	≤2 mΩ			
Stripping length	7.5 mm			
Material properties				
Material (contacts)	Copper alloy			
Surface (contacts)	Silver plated			
Material (locking)	Copper alloy			
Surface (locking)	Passivated			
RoHS	compliant with exemption			

ELV status compliant with exemption

Page 1 / 2 | Creation date 2024-02-10 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

6(c): Copper alloy containing up to 4 % lead by weight



Material properties

China RoHS	50			
REACH Annex XVII substances	Not contained			
REACH ANNEX XIV substances	Not contained			
REACH SVHC substances	Yes			
REACH SVHC substances	Lead			
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d			
California Proposition 65 substances	Yes			
California Proposition 65 substances	Lead Nickel			
Commercial data				

Packaging size	100
Net weight	2.46 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188631
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)