

Copy boring bar, right

For copy turning, internal, using XBGR indexable inserts

ORION[®]

Application:

For copy turning and longitudinal turning, external machining, using XBGR indexable inserts no. 17822

Execution:

- precision-engineered steel support with adjustable clamp, 93° pitch angle

Advantage:

- extremely flexible for contouring and easy accessibility, even for tricky contours
- top-quality and wear-resistant steel support and adjustable clamp



Art. no.	17822 208
Brand	ORION
Manufacturer Part Number	17822208
ISO name	S25R CXUB R/L
Shank diameter	25 mm
Length	200 mm
Programming size	16.5 mm
Machining direction	Right
Gross Weight	0.716 kg
Product Group	159

EAN

4053625120628