

Boring bar holder, shape E2

For turning tools with cylindrical shanks

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground
- Internal and external coolant supply



Art. no.	22778 106
Brand	ORION
Manufacturer Part Number	22778106
VDI mount diameter	25 mm
Clamping diameter	25 mm
Length	18 mm
Outer diameter	58 mm
Projecting length	60 mm
Gross Weight	1.168 kg
Product Group	2AC

EAN

4053625465040

