

swivel hoist ring, quality class 8

Screwed attachment point with ball bearing

CARTEC

Application:

Screw-on, rotating attachment point for lifting heavy loads that need to be rotated or turned. Suitable for safe lifting in accordance with Machinery Directive 2006/42/EC.

Version:

- quality class 8 - compact, lightweight design, with DGUV certification
- with ball bearing for easier loading, loadable in all directions
- Can be rotated by 360°, swivel range of bracket max. 180°
- Red, powder-coated surface
- permanent rotation under full load not permitted

Advantage:

- 4-way safety in every load direction
- constructed, tested and certified according to GS-OA 15-04 - EN 1677

Delivery:

Carrying capacities up to 35 t and other dimensions deliverable upon request.



Art. no.	77236 030
Thread dimension	M30
Load-carrying capacity	5300 kg
Internal width	45 mm
Bracket diameter	22 mm
Interior height	65 mm
Width of support plate	75 mm
Distance between lower edge of retainer holder and screw head	80 mm
Distance between lower edge of retainer holder and retainer	165 mm
Effective thread length	35 mm
Width across flats	65 mm
Colour	Red

EAN-Code

8013429800177