

Shrink-fit chuck

In accordance with ISO 7388-1 (DIN 69871)

diebold

Application:

For precise clamping of tools with straight shank h6.

Execution:

- Concentricity tolerance of hollow shank taper for location hole dia.< 0.003 mm.
- Clamping diameter for h6 shank tolerance.
- For higher speeds, fine balancing is necessary.
- Required pull stud no. 23690.

Delivery:

1x shrink-fit chuck in accordance with ISO 7388-1 (DIN 69871).



Art. no.	23425 568
Brand	DIEBOLD
Manufacturer Part Number	72.060.500.480
Tool holding device	SK 40
Clamping diameter	14 mm
Projecting length	160 mm
Tapered diameter	27 mm
Clamp in depth	47 mm
Form	AD
Concentricity tolerance	0.003 mm
Max. adjustment travel	10 mm
Coolant supply	Internal axial
Balancing quality	G 2.5 at 25 rpm
Gross Weight	1.600 kg
Product Group	297