

Manual lever snips 5 RP 10, for profile plates

For profile plates

Application:

For cutting sheet metal, flat, round, square, L or T-shaped sectional steel (not suitable for stainless steel sheets).


Execution:

- Robust shear body made from tempered steel
- Special tool steel blade, specially hardened and ground

Advantage:

- Lever arm with weight-equalising spring used as accident prevention
- With infinitely variable hold-down clamp for safe working processes

| | |
|--|------------------|
| Art. no. | 53790 040 |
| Model | 5RP 10 |
| Surface of the handle | Lacquered |
| Knife insert length | 175 mm |
| Max. material thickness for steel | 14 mm |
| Weight | 105 kg |
| Gross Weight | 103.000 kg |
| Product Group | 580 |



EAN

8695544460520